

Refrigeration

Product catalogue 2018















Refrigeration

20

23

Why choose Daikin?	4
Daikin Quality Philosophy	8
Eco-Design regulation	10
F-Gas regulation	12
Tools & Platforms	14

	Bi-Blocks	26
	Wine blocks	29
2	Condensing units	32
	Small CU	36
	Twin CU	41
	Large CU	42
	Booster CU	55

Plug and Play solutions

Uniblocks

for cold rooms and Wine rooms

3	Packs and Racks	58
	Multi compressor Racks	59
	Racks	64
4	Integrated Solutions - Refrigeration with Climatization	70
	Conveni-Pack + Booster	72
	Mix condensing units	78
5	Other products	80
6	Options	88
	ZEAS and Conveni-Pack	88
	Condensing units	90











Inverter technology

compressor

compressor

Reciprocating Swing compressor

compressor



We know refrigeration inside out

- We have over 100 years of experience in the Refrigeration business.
- We can meet all refrigeration needs from farm to fork,
 thanks to our wide range of refrigeration products.
- Innovative and Reliable own technology and expertise on Refrigerants, controls and compressors!
- Your advisor for solutions to meet your needs in line with legislation (F-gas regulation, ecodesign,...) and with focus on reliability, safety, Total Equivalent Warming impact (see page 7) and running cost.

Controlled temperatures throughout the whole supply chain



We can meet all refrigeration needs from farm to fork

Our extended product line-up is able to provide solutions for:

































Daikin Refrigeration – United in cold



Hubbard Products Ltd., is one of the UK's leading designers, manufacturers and suppliers of commercial cooling equipment and has earned an enviable Global reputation for innovation and designled excellence.



Daikin Chemicals

Daikin Chemicals is one of the world's foremost manufacturer of fluorochemical products and is a leading expert in that field. We strive to find new possibilities for living and industry by making the most of fluorine characteristics using our own exclusively developed technologies.



Daikin Europe N.V. is a major European producer of air conditioners, heating systems and refrigeration equipment, with approximately 5,500 employees throughout Europe and major manufacturing facilities based in Belgium, the Czech Republic, Germany, Italy, Turkey and the UK. Globally, Daikin is renowned for its pioneering approach to product development and the unrivalled quality and versatility of its integrated solutions.



Tewis is a leading company in the design and engineering of refrigeration systems. Along with their expertise in customising controls (including monitoring), Tewis offers total comprehensive solutions for Refrigeration and Climate applications. Over the last few years, Tewis has focused on developing a range of CO₂ based refrigeration systems and has established a long-lasting relationship with key Spanish and Portuguese food retailers. Its mission and philosophy to date has been to achieve high reliability and realise remarkable energy savings for their customer base.



Zanotti is a refrigeration specialist founded in 1962. With over 50 years of experience in food storing services covering the needs of commercial and industrial refrigeration, but also the needs of the transportation of fresh and frozen products. Zanotti changed the refrigeration world from the early days with the introduction of the Uniblock, an all in one plug and play refrigeration unit for cold rooms. Today they employ more than 600 people, with three production facilities and an annual turnover of approx 130 million Euro.




Meeting customer needs!

Depending on type of application, location and customers interest/values, the optimal refrigeration solution for the customer can potentially be different! **Thanks to our wide product portfolio, Daikin can offer what a customer really needs!**

The DNA of our Advice is:

Safety and Reliability

Reducing the Total Equivalent Warming Impact (TEWI)



Reduction of CO_2 emissions is one of the main priorities for the future. A refrigeration plant's global warming effect is the combination of the possible refrigerant losses (Direct warming impact) and the CO_2 emissions caused by electricity production (Indirect warming impact). Country per country situation is different, however on average in Europe CO_2 release at energy production is quite high (average 0,45kg/kwh of Electrical Energy)! Due to this, there is a significant greenhouse effect over the lifetime of the refrigeration plant and efficiency is thus one of the crucial focus points in reducing TEWI!

When various refrigeration solutions are being compared it is thus important to take into account both aspects as in some cases optimizing the direct warming impact (eg: changing refrigerant) will have an opposite effect on the indirect warming impact!

▼ Reducing your running cost

Through focus on reliability & quality, through extensive testing on each product, and energy efficiency our aim is to reduce your operational cost to the absolute minimum!






Daikin is committed to providing the most efficient and safe solutions to meet all of your refrigeration needs, today and in the future.

We are aware of our responsibility to protect the environment and our policies and practices keep environmental sustainability at the heart of everything we do. We conduct our business in accordance with green principles, because it makes economical as well as ecological sense.

Daikin Europe N.V. continually adapts its environmental policy to the changing global, European and local legislative frameworks. It stimulates and promotes the strict application of all relevant legislation and formulates recommendations to facilitate implementation.

Tests during development and during production, to evaluate the performance of our products so that they meet the envisioned capacities, energy efficiency and reliability, is the foundation of our quality philosophy!

Each unit leaving production on our factory line in Oostende - Belgium, has been rigorously tested from design stage (eg: vibration test) up to final production (each and every unit has a leakage test, electrical test and a running test)! As units can be exposed to severe weather conditions during the lifetime of the equipment, they are foreseen with anti-corrosion treatments and resistant casing to ensure a long life!






See how transportation is simulated and vibrations are tested on our shaker (search: vibration ZEAS)









Vibration damper assembly



Logical, orderly and "tidy" installation in the control cabinet



Everything cleanly processed with high quality



Easily accessible and clearly laid out compound machines





Ecodesign Directive - Energy related products

The EU's Ecodesign Directive 2009/125/EC is designed to encourage the market to use more efficient products. It also helps manufacturers to agree a better definition of efficiency for remote condensing units. Since 01/07/2016 refrigeration units also need to comply with this system of minimum efficiency requirements.

In catalogues the seasonal data will be marked with the seasonal flower.

Find more information about the seasonal data in refrigeration on our website: www.daikin.eu or on the Business Portal my.daikin.eu

EN 13215:

Definition of the nominal operating conditions (capacity, COP and power consumption)

Temperature application	Medium	Low						
Ambient temperature	32°C	32°C						
Evaporation temperature	-10°C	-35°C						
Suction gas side	10 K superheat OR 20°C suction gas temperature							
Subcooling degree of the liquid	Depending on the condenser coil used in the refrigeration system							

To define the efficiency of a condensing unit the Ecodesign Directive used the EN13215 regulation. Both methodologies are allowed to define delivered cooling capacity and efficiency of a unit.

→ This has also an impact on the SEPR AND COP value.

Two methodologies to evaluate the unit performance

Low capacitiesCondensing unit installed indoor

COP methodology:

- If the medium temperature cooling capacity is lower than 5 kW and low temperature cooling capacity is lower than 2 KW
- > COP given on 25°C ambient temperature
- > COP given on 32°C ambient temperature
- > COP given on 43°C: mandatory if ambient temperature design is higher or equal to 35°C

Minimum efficiency (COP):

- Medium temperature:
 Capacity lower or equal 1 kW = 1.2
 Capacity lower or equal 5 kW = 1.4
- Low temperature:
 Capacity lower or equal 1 kW = 0.75
 Capacity lower or equal 2 kW = 0.85

Higher capacities Condensing unit installed outdoors (climate depending)

SEPR methodology:

- If the medium temperature cooling capacity is between 5kW and 50kW and low temperature cooling capacity is between 2kW and 20kW
- SEPR given on the reference climate zone of Strasbourg
- > COP given on 43°C: mandatory if ambient temperature design is higher or equal to 35°C

Minimum efficiency (SEPR):

- Medium temperature:
 Capacity lower or equal 20 kW = 2.25
 Capacity lower or equal 50 kW = 2.35
- Low temperature:
 Capacity lower or equal 8 kW = 1.5
 Capacity lower or equal 20 kW = 1.6

Daikin refrigeration product portfolio and Ecodesign Directive



Model	MONOBLOCKS BIBLOCKS	JEHCCU	MINI ZEAS	ZEAS	MULTI ZEAS	CONVENI-PACK	BOOSTER		OTHER RANGES		
Model	WINEBLOCKS	JEHSCU	MINI ZEAS	ZENJ	MOLITZEAS	CONVENI-FACK	BOOSTER	Refrigerating capacity <20kw	Refrigerating capacity < 50kw	Refrigerating Capacity >50kW	
Medium temperature (Te = -10°C)	out of scope	in scope	in scope	in scope	out of scope ⁽¹⁾	out of scope ⁽²⁾	-	in scope	in scope	out of scope	
Low temperature (Te = -35°C)	out of scope	in scope	in scope	in scope	out of scope ⁽¹⁾	-	out of scope ⁽³⁾	in scope	out of scope	out of scope	

- (1) Delivered capacity of the multi Zeas units in medium and low temperature application are higher than the upper boundary (MT: Q > 50 kW; LT: Q > 20 kW) mentioned in the Ecodesign
- (2) The CVP can only operates when also Daikin indoor units are connected. This means that the CVP can be seen as a condensing unit with multiple condensers which is considered out of scope of the Ecodesign Directive ENTR LOT1
- (3) The booster unit is not seen as a condensing unit, because the heat extracted from the evaporator side is (LT –side) discharge in the MT refrigerant line of a CVP or Zeas unit and not to the surrounding air as described in the Ecodesign Directive ENTR LOT1



What does the F-Gas regulation mean?




Ban from the year 2020 onwards

in $\underline{\text{new}}$ stationary refrigeration equipment

Ban from the year 2030 onwards

in <u>servicing existing</u> stationary refrigeration equipment


F-Gas Regulation




^{*&}quot;Multipack centralised refrigeration systems" = Systems with two or more compressors operated in parallel, which are connected to one or more common condensers and to a number of cooling devices such as display cases, cabinets, freezers or to chilled store rooms.










Tools and platforms



We offer a varier simulation and your sales.





Sales supporting apps

We offer a variety of building modelling, selection, simulation and quotation software tools to support your sales.

Refrigeration Xpress selection software

User-friendly selection software for Conveni-Pack, JEHCCU / JEHSCU, monoblocks, bi-blocks and ZEAS condensing units. Its detailed report includes a list of materials, piping and wiring diagrams, and device options. Design software available for Conveni-Pack and Zeas condensing units.

Psychrometric Diagram Viewer

The **Psychrometric Diagram Viewer** helps designers, consultants, students and other professionals to get more insight in our fields of activities: "the air that we condition"

Selection software

In order to obtain a precise selection of the refrigeration capacity and the equipment as well as to be able to select further products from our product range, we recommend our Technoblock selection software.

Please contact your local Daikin refrigeration sales team for more information.




Where to download the software? Where to find catalogues and data books?

- > Experience our business platform that thinks with you at my.daikin.eu
- > Find information in seconds via a powerful search
- > Customise the options so you see only info relevant for you
- > Access via mobile device or desktop

Register and login on my.daikin.eu and get what you want!

Find our solution for different applications:





Quick selection guides for Uniblocks and Wineblocks





E-Care APP

Easy access to all the information about your unit, in mobile format. Daikin e-Care app incl. functionalities such as:

- > Product registration
- > e-Configurator
- > e-Doctor






















		Technolog	gy compressor	Page		Hermetic		Semi-h	ermetic		Capacity	y control	
		Application	Refrigerant		Reciprocating compressor	Rotary	Scroll	Reciprocating compressor	Screw	Varispeed	External frequency drive	DC control	Digital scroll
ne rooms	Uni-block	MT	R134a R407C R407H	22-25 22-25 22-25	•		•						
Plug & Play solution for cold room & wine rooms		LT	R290) R452A R407F	22-25 22-25 22-25	•		•						
n for co	Biblock	MT	R290) R134a	22-25 26-28	•								
solutio	6 00	LT	R452A	26-28	•								
Plug & Play	Wineblock	HT Cooling	R407F R134a	26-28	•								
	Single CU (ON/OFF or INVERTER)	MT	R449A* R134a R410A	34-40 34-40 44	•		•	•		•	•	•	•
	01 :: 6		R449A* R407F	54 34-40 34-40	•	•	•	•		•	•	•	
	Twin CU	LT	R410A (CO ₂) R449A*	54 41	•	•	•	•		•	•	•	•
Condensing units	00	MT	R134a R410A	41 44 54	•		•	•		•	•	•	•
Conde		LT	R449* R407F R410A	41 41 44	•		•	•		•	•	•	
	Multi CU	MT	R449A R410A	42-43 44 54			•	•		•	•	•	•
	The last of the la	LT	R449A R410A	42-43 44			•			•	•	•	
	Booster CU (MT + LT)	MT	FRAS CO.	55-57				•			•		
	Racks	LT	R449A	55-57 59-61	•		•	•	•	•	•		•
acks		MT	R134a	59-61	•		•	•	•	•	•		•
k and p	-	LT	R449A R407F	59-61 59-61	•		•	•	•	•	•		
Compressor rack and packs		MT	FRAE CO,	64-65				•			•		
Com		MT	FGAS CO.	66				•			•		
	Conveni-pack	LT MT	R410A	66 72			•	•			•	•	
ou)		LT	R410A	72			•					•	
ons atisati		AC	R410A	72 72			•					•	
solutic od clima	MIX CU	HR + HP	R410A	72 78-79			•	•			•	•	
egratec ation ar		MT	FRAS CO,	78-79				•			•		
Integrated solutions (Refrigeration and climatisation)	MIX RACK	AC	GFGAS CO.	78-79				•			•		
		MT	FGAS CO.	78-79				•			•		








LMCLN-AV3/AW1 and LMCMD-AV3/AW1

Uni-block system for low and medium temperature refrigeration

For roof mounted installation in small and medium sized cold rooms

- > Rapid mounting on the roof of the cold room
- Ceiling assembly leaves the space inside the cold room completely free
- > The white colour of the evaporator blends unobtrusively with the cold room walls
- > Extremely fast to assemble, reducing installation time and cost
- > Best surface-to-capacity ratio
- > Remote electronic command station with easy-to-use user interface programmable according to various system requirements








Low Temperature F	Refrigeration			LMCLN	100AV3	170AV	3	200AW1	300AW1
Refrigerating capacity	Low temperature	R-452A	Nom	kW	0.565	0.931		1.527	2.212
Recomm. Cold Room Volu	me Low temperature	V 100		m³	2.1	5		11.4	20.2
Power input	Max.			w	910	1,970		2,540	3,210
Dimensions	Unit	HeiahtxV	/idthxDepth	mm	690x830x540	660x790x	730	690x880x930	800x1,000x930
Weight	Unit			kg	48.0	68.0		87.0	102.0
	Packed uni	t .		kg	61.0	82.0		222.0	124.0
Compressor	Туре	-					Hermetic Reciproca	tina	
	Piston disp	lacement		m³/h	3.03	5.99		8.4	12.9
Defrost				,			Hot gas		
Evaporator	Air flow			m³/h	500	550		1,100	2,300
_ rapolator	Air throw			m	3	330	4	171.00	9.5
Refrigerant	Type/GWP						R-452A/2,141		,,,
gerane	Charge			kg/TCO2Eq	0.500/1.071	0.420/0.8		0.720/1.542	0.960/2.055
Power supply	Phase/Freq	μορον/Volt	200	Hz/V		~/50/230	,,	3~/50/4	
Medium Temperati				LMCMD	050AV3	060AV3	075AV3	100AV3	122AV3
Refrigerating capacity	Medium temperature		Nom	kW	0.836	1.091	1.302	1.761	1.979
Recomm. Cold Room Volu	me Medium temperature	V 100		m³	5.7	8.3	10.8	16.4	18.3
Power input	Max.			W	1,230	1,480	1,740	1,900	2,350
Dimensions	Unit	HeightxV	/idthxDepth	mm	690x830x540	660x79	660x790x730		
Weight	Unit			kg	42.0	59.0		74.0	75.0
	Packed uni	t		kg	55.0	73	95.0	97.0	
Compressor	Type						Hermetic Reciproca	iting	
	Piston disp	lacement		m³/h	3.8	4.52	5.69	6	8.36
Defrost							Hot gas		
Evaporator	Air flow			m³/h	500	55	0		1,100
	Air throw			m	3			4	
Refrigerant	Type/GWP						R-134a/1,430		
	Charge			kg/TCO2Eq	0.550/0.787	0.540/0.772	0.600/0.858	0.730/1.044	0.700/1.00
Power supply	Phase/Freq	uency/Volt	age	Hz/V			1~/50/230		
	D. 6	•		LMCMD	4208144	4 50 8141		2008184	200 81414
Medium Temperati			N	LMCMD	120AW1	150AW	1	200AW1	300AW1
Refrigerating capacity	Medium temperature		Nom	kW	1.979	3.209		3.482	4.752
Recomm. Cold Room Volu		V 100		m³	18.3	36.9		41.1	61.1
Power input	Max.	11.2.1.4.14	rad Dood	W	2,430	2,930	000 1 000 000	3,220	3,670
Dimensions	Unit	HeightxV	/idthxDepth	mm	690x880x930		800x1,000x930		920x1,120x1,200
Weight	Unit			kg	75.0	92.0		93.0	151.0
	Packed uni	1		kg	87.0	114.0		115.0	184.0
Compressor	Type	•		3			Hermetic Reciproca		44.04
	Piston disp	lacement		m³/h	8.36	9.37		10.52	11.81
Defrost -				3			Hot gas	i	
Evaporator	Air flow			m³/h	1,100		2,300		3,450
	Air throw			m	4		R-134a/1,430	9.5	
Refrigerant	Type/GWP								
	Charge			kg/TCO2Eq	0.700/1.001	1,150.000/1		1.100/1.573	2.000/2.860
Power supply	Dlanes/Funn	uency/Volt	200	Hz/V			3~/50/400		

Uni-block system for low and medium temperature refrigeration

For wall mounted installation in small and medium sized cold rooms

- > Rapid mounting on the wall of the cold room by straddlemounting, which is ideal for new installations or through-wall mounting, which is ideal for refurbishment projects
- > Metallic grey coloured finish of the outdoor unit
- > The white colour of the evaporator blends unobtrusively with the cold room walls
- Compressor compartment insulated with suitable soundproofing material to reduce sound levels
- Microchannel condensers available in order to reduce the refrigerant charge as much as possible and ensuring higher energy efficiency
- > The units are provided with a new generation control panel with an easy-to-use interface







Low Temperature	Refrigeration		LMSLN	100AV3	120AV3	170AV3	172AV3	200AW1	300AW1	
Refrigerating capacity	Low temperature	R-452A No	m kW	0.579	0.807	0.922	1.193	1.526	2.090	
Recomm. Cold Room Volu	ume Low temperature	V 100	m³	2.2	3.9	4.9	7.6	11.4	18.1	
Power input	Max.		W	910.00	1,300.00	1,300.00 2,000.00		2.54	3.20	
Dimensions	Unit	HeightxWidthx	Depth mm		930x925x530		930x9	25x865	1,030x1,150x840	
Weight Unit		kg	60.0	6	1.0	78.0	80	114		
	Packed unit	Packed unit		75.0	76.0		95.0	97	133	
Compressor	Type			Hermetic Reciprocating						
	Piston displ	acement	m³/h	3.03	4.54 5.99			8.3	12.9	
Defrost						Но	t gas			
Evaporator	Air flow		m³/h		530	1,0)50	1,370		
	Air throw		m			5		5	8	
Refrigerant						R-452	A/2,141			
	Charge		kg/TCO2Eq		0.600/1.285		0.890/1.905	0.900/1.93	1.750/3.75	
Power supply	Phase/Freq	uency/Voltage	Hz/V		1~/5	1~/50/230				

Medium Temperat	ure Refrigeration	LMSMD	030AV3	050AV3	060AV3	075AV3	100AV3	102AV3	122AV3		
Refrigerating capacity	Medium temperature R-134a Nom	kW	0.838	0.952	1.112	1.388	1.491	1.768	1.920		
Recomm. Cold Room Volu	ume Medium temperature V 100	m³	5.7	6.8	8.6	11.8	13.0	16.5	18.5		
Power input	Max.	W	970	1,220	1,430	1,690	1,780	1,890	2,330		
Dimensions	Unit HeightxWidthxDep	th mm			930x925x530			930x925x0.865			
Weight	Unit	kg	48		49 54 55			73			
	Packed unit	kg	63	64		69	70	9	90		
Compressor	Type		Hermetic Reciprocating								
	Piston displacement	m³/h	2.53	3.8	4.52	5.69 6.		.00	8.36		
Defrost						Hot gas					
Evaporator	Air flow	m³/h			530			1,0	050		
	Air throw	m	5								
Refrigerant	Type/GWP					R-134a/1,430					
	Charge	kg/TCO2Eq		0.680/0.972		0.650)/0.930	0.850/1.216	0.780/1.115		
Power supply	Phase/Frequency/Voltage	Hz/V				1~/50/230					

1 ower suppry	Thase/Trequency/Voltage	112/ ¥		1 750	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,				
Medium Temperat	ture Refrigeration	LMSMD	120AW1	130AW1	150AW1	200AW1			
Refrigerating capacity	Medium temperature R-134a Nom	kW	1.992	2.275	3.129	3.430			
Recomm. Cold Room Volu	ume Medium temperature V 100	m³	18.5	22.7	35.7	40.3			
Power input	Max.	W	2,420	2,790	3,070	3,380			
Dimensions	Unit HeightxWidthxDepth	mm	930x9	25x865	1,030x1,	150x840			
Weight	Unit	kg	73	75	91	93			
	Packed unit	kg	90	92	110	112			
Compressor	Type			Hermetic Re	ciprocating				
Joinpressor	Piston displacement	m³/h	8.36	9.37	10.52	11.81			
Defrost				Hot	gas				
Evaporator	Air flow	m³/h	1,0	050	1,370				
	Air throw	m		5		3			
Refrigerant	Type/GWP			R-134a/	1,430.0				
	Charge	kg/TCO2Eq	0.8/	1.115	1.6/2.288				
Power supply	Phase/Frequency/Voltage	Hz/V		3~/50/400					

LMDMD-AW1


Uni-block system for low and medium temperature refrigeration

For wall mounted installation in medium sized cold rooms

- > Rapid mounting on the wall of the cold room by through-wall
- > Extremely fast to assemble, reducing installation time and cost
- > The white colour of the evaporator blends unobtrusively with the cold room walls
- > Very compact and very efficient
- Remote electronic command station with easy-to-use user interface programmable according to various system requirements

POAMIN LMDMD-AWI

Installation type



Low and medium te	mperature refriger	ration	LMDI	ND-AW1	350	400	600	750		
Refrigerating capacity	Medium temperature	R-134a	Nom	kW	4.981 (2)	6.988 (2)	8.290 (2)	10.664 (2)		
Dimensions	Unit	Height x W	Height x Width x Depth mm		857 x 1,280 x 1,140	857 x 1,7	50 x 1,140	857 x 1,790 x 1,240		
	Packed unit	Height x W	Height x Width x Depth mm		1,060 x 1,330 x 1,210	1,065 x 1,8	350 x 1,300	1,065 x 1,850 x 1,420		
Weight	Unit			kg	162	221	222	244		
	Packed unit			kg	202	276	277	361		
Compressor	Туре					Hermetic Re	eciprocating			
_	Nominal power			kW	3.7	4.8	6.3	7.4		
	Starting method					Dia	rect			
Operation range	Cold room temperature	Min. ~Max	х.	°C		-5	~10			
Refrigerant	Туре				R-134a					
	GWP					1,4	130			
Evaporator	Air flow			m³/h	3,900	5,6	500	8,000		
	Air throw			m		10 (3)		17 (3)		
Condenser	Air flow			m³/h	2,700	4,0	5,600			
Defrost						Hot	: gas			
Power supply	Voltage/Phase/Fre	quency		V/Hz		400/3	N~ / 50			

⁽¹⁾ When normally running: -20°C / +30°C

⁽²⁾ When normally running: 0°C / +30°C

⁽³⁾ Use air throw as a base. Air throw is affected by many factors such as height of room, product storage, location of evaporator, etc.



Bi-block system for low and medium temperature refrigeration

Condensing unit for floor standing or roof mounted installation

- Condensing unit for floor standing or roof mounted installation and ceiling mounted evaporator
 Thermostatic expansion valve ensuring optimum capacity in accordance with the required load for better energy efficiency
- > Extremely fast to assemble thanks to quick connection joints
- > Reduced installation time and cost
- > Best surface-to-capacity ratio







Low Temperature	Refrigeration	SB.LBCLN	100AV3	120AV3	170AV3	172AV3	200AW1	300AW1
Refrigerating capacity	Low temperature R-452A Nom	kW	0.579	0.807	0.970	1.193	1.526	2.090
Recomm. Cold Room Volu	ume Low temperature V 100	m³	2.2	3.9	5.3	7.6	11.4	18.1
Power input	Max.	W	950	1,330	2,000	2,080	2.590	3.360
Dimensions	Condensing unit HeightxWidthxDepth	mm			640x690x860			740x760x960
	Evaporator unit HeightxWidthxDepth	mm		360x690x545		360x9	90x545	360x1,440x545
Weight	Condensing unit	kg	50	5	2	63	65	85
	Evaporator unit	kg		9		1	24	
	Packed condensing unit	kg	66.0	68	3.0	79.0	81.0	101.0
	Packed evaporator unit	kg	11.5			18	3.9	27.6
Compressor	Type		Hermetic Reciprocating					
	Piston displacement	m³/h	3.03	4.54	5.99		8.3	12.9
Defrost					Elec	ctric		
Evaporator	Air flow	m³/h		730		1,3	360	2,060
	Air throw	m			(5		
Refrigerant	Type/GWP				R-452	N/2,141		
-	Charge	kg/TCO2Eq		0.93/1.991		1.6/3	3.426	2.3/4.924
Power supply	Phase/Frequency/Voltage	Hz/V		1~/50	0/230		3~/	50/400

Medium Temperat	ure Refrigeration	SB.LBCMD	050AV3	060AV3	075AV3	100AV3	122AV3		
Refrigerating capacity	Medium temperature R-134a Nom	kW	0.952	1.112	1.388	1.768	1.992		
Recomm. Cold Room Volu	ume Medium temperature V 100	m³	6.8	8.6	11.8	16.5	18.5		
Power input	Max.	W	1,250	1,460	1,720	1,930	2,460		
Dimensions	Condensing unit HeightxWidthxDepth	mm			640x690x860				
	Evaporator unit HeightxWidthxDepth	mm		360x690x545		360x9	90x545		
Weight	Condensing unit	kg		41	44	6	52		
	Evaporator unit	kg		9		1	6		
	Packed condensing unit	kg	5	57.0	60.0	78	3.0		
	Packed evaporator unit	kg		11.5		18	3.9		
Compressor	Type				Hermetic Reciprocating				
	Piston displacement	m³/h	3.8	4.52	5.69	6	8.36		
Defrost					Electric				
Evaporator	Air flow	m³/h		730		1,3	360		
	Air throw	m			6				
Refrigerant	Type/GWP				R-134a/1,430				
	Charge	kg/TCO2Eq		0.93/1.333		1.6/2	2.288		
Power supply	Phase/Frequency/Voltage	Hz/V			1~/50/230				

Power supply	Phase/Frequency/Voltage	Hz/V			1~/50/230		
Medium Temperat	ture Refrigeration	SB.LBCMD	120AW1	150AW1	151AW1	200AW1	201AW1
Refrigerating capacity	Medium temperature R-134a Nom	kW	1.992	3.1	29	3.4	30
Recomm. Cold Room Volu	ume Medium temperature V 100	m³	18.5	35	.7	40	.3
Power input	Max.	W	2,380	3,230	3,150	3,530	3,450
Dimensions	Condensing unit HeightxWidthxDepth	mm	640x690x860		740x7	60x960	
	Evaporator unit HeightxWidthxDepth	mm	360x990x545	360x1,440x545	710x970x770	360x1,440x545	710x970x770
Weight	Condensing unit	kg	62	75	81	77	88
	Evaporator unit	kg	16	24	40	24	40
	Packed condensing unit	kg	78.0	92.0	98.0	94.0	105.0
	Packed evaporator unit	kg	18.9	27.6	56.0	27.6	56.0
Compressor	Type				Hermetic Reciprocating	1	
	Piston displacement	m³/h	8.36	10.	52	11.	81
Defrost					Electric		
Evaporator	Air flow	m³/h	1,360	2,060	2,320	2,060	2,250
	Air throw	m		6	13	6	13
Refrigerant	Type/GWP				R-134a/1,430		
	Charge	kg/TCO2Eq	1.6/2.288		2.3/	3.289	
Power supply	Phase/Frequency/Voltage	Hz/V			3~/50/400		

Bi-block system for low and medium temperature refrigeration

Condensing unit for floor standing or roof mounted installation

- Condensing unit for floor standing or roof mounted installation and ceiling mounted evaporator
- > Extremely fast to assemble thanks to quick connection joints
- > Reduced installation time and cost
- > Best surface-to-capacity ratio



Low Temperature Re	frigeration	SB.L	BTLN-AV3/AW1		100			120			170			172			200			300		
				1	2	3	1	2	3	1	2	3	1	2	3	1	2	3	1	2	3	
Refrigerating capacity	Low temperature R-452A	Nom	kW		0.579			0.807			970			1.193			1.526			2.09	0	
Recomm. Cold Room Volume	Low temperature V 100		m³		2.2			3.9			5.3			7.6			11.4			18.1	ı	
Power input	Max.		W		950			1,330			2,000			2,080			2,590			3,360	0	
Dimensions	Condensing unit HeightxWid	lthxDepth	mm		640x690x860													740	x760)x960		
	Evaporator unit HeightxWid	•	mm							360	x690x5	45							360x	1.440	0x545	
Weight	Condensing unit		kg		50.0				53	2.0				63.0			65			85		
g.n.	Evaporator unit		kg		50.0			9.0						03.0	16	. 0				24		
	Packed condensing unit		kg		66.0			7.0	69	8.0				79.0	- 10		81.0			102.0		
	Packed evaporator unit		kg		00.0			11.5	00	5.0				18.9			18.9			27.6		
C			ку	-				11.5			Hamas	4: - D-					10.9			27.0	,	
Compressor	Type		34.		2.02			454		T	Herme			ating			0.2			12.0		
_ ,	Piston displacement		m³/h		3.03			4.54				5.9					8.3			12.9	,	
Defrost -			2.0									Elec	tric									
Evaporator	Air flow		m³/h					730							1,3	60				2,060	0	
	Air throw		m									6										
Refrigerant	Type/GWP										R-	452A	2,141.0	0								
	Charge		kg/TCO2Eq				0).715/1.5	31						1.280/	2.740			1.5	00/3	.212	
Piping Length			m	2.5	5	10	2.5	5	10	2.5	5	10	2.5	5	10	2.5	5	10	2.5	5	10	
Power supply	Phase/Frequency/Voltag	je	Hz/V									1~/50	0/230									
Medium Temperatur	e Refrigeration		SB.LBTMD-AV3		050				060			07	75			100			1	22		
				1	2	3	3	1	2	3	1	2	2	3	1	2	3	1		2	3	
Refrigerating capacity	Medium temperature R-134a	Nom	kW		0.95	2			1.112			1.3	88			1.768	3		1.	992		
Recomm. Cold Room Volume	Medium temperature V 100		m³		6.8				8.6			11	.8			16.5			1	8.5		
Power input	Max.		W									1,7				1,930)			460		
Dimensions		lthvDenth	mm		.,25				.,		- 6					.,,,,,,		2,400				
Difficusions	Condensing unit HeightxWidthxDepth mm Evaporator unit HeightxWidthxDepth mm				640x690x860 360x690x545 360x990x545											AE.						
\\/_:_L+	, ,										4	4					62.0	43				
Weight	Condensing unit		kg				41.	.0	0.0			4	4									
	Evaporator unit		kg	9.0							16.0											
	Packed condensing unit		kg				57.	.0								78						
	Packed evaporator unit		kg															18.9				
Compressor	Туре									Hermetic			ciproc	ating								
	Piston displacement		m³/h	3.8 4.52								5.6	59			6			8	.36		
Defrost					Electric																	
Evaporator	Air flow		m³/h						730									1,360	50			
·	Air throw		m					6														
Refrigerant	Type/GWP										R	-134a	/1,430									
	Charge		kg/TCO2Eq					0.7	15/1.0	22	-					1.280/1.8			920			
Piping Length	Charge		m m	2.5	5	1	0	2.5	5	10 2.5 5 10										5	10	
Power supply	Phase/Frequency/Voltag	10	Hz/V	2.5		- 1	0	2.5		10		1~/50		10	2.5		10		<i>y</i>		10	
rower supply	rnase/rrequency/voltag	je	П2/ V									1~/30	J/23U									
Medium Temperatur	e Refrigeration		SB.LBTMD-AW1			12	20					15	50					20	0			
				•	1	2	2	3	3	1		2	2	3			1	2	2		3	
Refrigerating capacity	Medium temperature R-134a	Nom	kW			1.9	92					3.1	29					3.4	30			
Recomm. Cold Room Volume	Medium temperature V 100		m³			18	3.5					35	5.7					40	.3			
Power input	Max.		W			2,3						3,2										
Dimensions	Condensing unit HeightxWid	lthyDenth	mm		-	540x69		50				5,2			3,530 740x760x960							
Difficusions	Evaporator unit HeightxWid		mm			360x99									60x1,4							
\\/_:_L+		шхрерш		-				+3				7	_		00X 1, 4	40834		7	,			
Weight	Condensing unit		kg	_		6							э						/			
	Evaporator unit		kg			1									2	4						
	Packed condensing unit		kg			78						92	2.0					94	.0			
	Packed evaporator unit k					18	3.9								27.6							
Compressor	Туре								Herme			ating										
	Piston displacement n					8.3	36			10.52						11.81						
Defrost					Electric																	
Evaporator	Air flow	m³/h	1,360								2,0	60										
*	Air throw							6							2,060							
	Type/GWP										R-134a/1,430											
Refrigerant																						
Refrigerant			kn/TCO2Fn																			
	Charge		kg/TCO2Eq		5				0	7	5						5		: 1		10	
Refrigerant Piping Length Power supply			kg/TC02Eq m Hz/V	2	.5		5	1	0	2.		3~/50	5	1			.5	5	;		10	




Wineblock - Monoblock units for high temperature refrigeration

Monoblock system suitable for through-wall installation

- > Accurate humidity and temperature control to guarantee the quality of products (e.g. wines)
- > Integrated humidifier available depending on model to have one unit which covers it all: perfect humidity & temperature control
- > Electronic controller managing both temperature and humidity of the cold room



Installation type



High Temperature	Refrigeration		LMSWHD-A	V3018/AV3118	030	050	060	075
Refrigerating capacity	High temperature	R-134a	Nom	kW	0.60 (1)	1.00 (1)	1.40 (1)	2.00 (1)
Heating capacity	R-134a Nom			kW	0.70	1.05	1.40	1.75
Power input	Max.			W	1,210	1,690	2,310	2,780
Range RH%				%		60	-80	
Dimensions	Unit	HeightxW	idthxDepth	mm	735x4	00x435	735x62	20x435
	Packed unit	HeightxW	idthxDepth	mm	955x4	95x435	955x49	95x655
Weight	Unit			kg	49	52	77	79
	Packed unit			kg	59	62	89	91
Compressor	Type					Hermetic R	eciprocating	
	Piston displ	acement		m³/h	1.4	2.3	3.8	5.7
Condenser	Air flow			m³/h	60	00	1,2	00
Defrost						Į.	Air	
Evaporator	Air flow			m³/h	60	00	1,2	00
Operation range	Cold room temperature	Min.~Max		°C		10	~20	
	Ambient temperature	Min.~Max		°C		10	~40	
Refrigerant	Type/GWP					R-134	a/1,430	
	Charge			kg/TCO2Eq	0.43/0.61	0.38/0.54	0.45/0.64	0.60/0.86
Power supply	Phase/Freq	uency/Volta	age	Hz/V		1~/5	0/230	

SB.LBCWHD-AV30DR/31DR


Wineblock - Split units for high temperature refrigeration

Compact condensing unit and small-sized ceiling mounted evaporator

- > Accurate humidity and temperature control to guarantee the quality of products. Best for wine conservation and refinement.
- > Thermostatic expansion valve ensuring optimum capacity in accordance with the required load for better energy efficiency
- > Integrated humidifier available depending on model to have one unit which covers it all: perfect humidity & temperature control
- > Electronic controller managing both temperature and humidity of the cold room



Installation type



High Temperature Re	efrigeration	SB.LBCWHDAV30DR/31DR*	030	050	060	075
Refrigerating capacity	High temperature R-134a	Nom kW	0.60 (1)	1.00 (1)	1.40 (1)	2.00 (1)
Heating capacity	R-134a Nom	kW	0.90	0	1.6	50
Power input	Max.	W	1.42	1.55	2.44	2.55
Range RH%		%		60-	80	
Dimensions	Condensing unit HeightxW	idthxDepth mm	357x682	2x337	390x88	32x427
	Evaporator unit HeightxW	idthxDepth mm	215x669	9x490	215x1,0	89x490
	Packed condensing unit HeightxW	idthxDepth mm	590x400	0x800	610x51	0x1,000
	Packed evaporator unit HeightxW	idthxDepth mm		540x250	0x1,190	
Weight	Condensing unit	kg	33	36	61	63
	Evaporator unit	kg	13		1	9
	Packed condensing un	it kg	38	41	68	70
	Packed evaporator uni	t kg	14.	5	2	2
Compressor	Туре			Hermetic Re	ciprocating	
	Piston displacement	m³/h	1.4	2.3	3.8	5.7
Condenser	Air flow	m³/h	600)	1,2	00
Defrost				A	ir	
Evaporator	Air flow	m³/h	600)	1,2	00
Operation range	Cold room temperature Min.~Max	. ℃		10~	·20	
	Ambient temperature Min.~Max	. ℃		10~	40	
Refrigerant	Type/GWP			R-134a	/1,430	
	Charge	kg/TCO2Eq	1.3/1	.86	1.8/2	2.57
Power supply	Phase/Frequency/Volta	ige Hz/V		1~/50	0/230	

(1)When normally running: $+14^{\circ}\text{C} / +30^{\circ}\text{C}$

 $[\]star$ SB.LBCWHD-AV30DR: Unit with humidifier kit included; SB.LBCWHD-AV31DR: Unit without humidifier kit.

Wineblock - Split units for high temperature refrigeration

Compact condensing unit and small-sized wall mounted evaporator


- Accurate humidity and temperature control to guarantee the quality of products. Best for wine conservation and refinement.
- Thermostatic expansion valve ensuring optimum capacity in accordance with the required load for better energy efficiency
- > Integrated humidifier available depending on model to have one unit which covers it all: perfect humidity & temperature control
- > Electronic controller managing both temperature and humidity of the cold room




High Temperature R	efrigeration	SB.LBWWH	D-AV3096/3196	030	050	060	075
Refrigerating capacity	High temperature R	-134a Nom	kW	0.60	1.00	1.40	2.00
Heating capacity	R-134a N	lom	kW	0.70	1.05	1.40	1.75
Power input	Max.		W	1.23	1.71	2.26	2.72
Range RH%			%		60-	-80	
Dimensions	Condensing unit H	leightxWidthxDepth	mm	357x68	32x337	390x88	32x427
	Evaporator unit H	leightxWidthxDepth	mm	570x37	75x210	570x59	95x210
	Packed condensing unit	leightxWidthxDepth	mm	590x40	00x800	610x51	0x1,000
	Packed evaporator unit	leightxWidthxDepth	mm	610x25	50x525	610x25	50x745
Weight	Condensing u	nit	kg	33.0	36.0	61.0	63.0
	Evaporator un	it	kg	13	3.0	19	0.0
	Packed conde	nsing unit	kg	38.0	41.0	68.0	70.0
	Packed evapo	rator unit	kg	14	l.5	21	.0
Compressor	Type				Hermetic Re	ciprocating	
	Piston displace	ement	m³/h	1.4	2.3	3.79	5.7
Condenser	Air flow		m³/h	60	00	1,2	00
Defrost					A	ir	
Evaporator	Air flow		m³/h	60	00	1,2	00
Operation range	Cold room temperature N	lin.∼Max.	°C		10~	-20	
	Ambient temperature N	lin.∼Max.	℃		10~	-40	
Refrigerant	Type/GWP				R-134a/	1,430.0	
	Charge		kg/TCO2Eq	1.3/	1.86	1.8/	2.57
Power supply	Phase/Freque	ncy/Voltage	Hz/V		1~/50	0/230	

(1)When normally running: +14°C / +30°C

^{*}SB.LBWWHD-AV3096: Unit with humidifier kit included; SB.LBWWHD-AV3196: Unit without humidifier kit.







Why Daikin condensing units?

Daikin's commercial condensing units are ideal for use in cold stores, pubs, hotels, butchers, bakeries and similar locations which need reliable cooling at medium temperature.


- Daikin JEHCCU and JEHSCU series plug-in condensing units are the perfect solution for those looking for compact and economically priced solutions.
- Highly energy-efficient with operating ambient temperatures ranging from
 -15°C to +43°C.
- Daikin condensing kits are suitable for refrigerants R-407F, R-407A, R-404A, R-134a and latest low GWP refrigerants R-448A and R-449A
- > Carefully designed details: the whole range utilizes proven and specially optimized components for Daikin.

- > Fast assembly, easy handling and an energy-optimized design ensure low investment and operating costs
- > Redesigned to be lightweight and compact, with easy access, making installation and maintenance straightforward.
- > Improved design and sound insulation make them ideal for urban locations, particularly near residential areas.



	Scroll compressor	Reciprocating compressor	230 V current	400 V current			244	4.0	4075		D 407A		0.12				VE			4524
			23	40		= R4	J4A	▲ = R	-40/F		R-407A		= R-134		x = R-4	148A	★ = R-4	149A	*= K	R-452A
MT cooling					<1	1	2	3	4	5	Ketrig 6	eration 7	capacit 8	9 (KW)	10	11	12	13	14	15
JEHCCU 0040 CM1		•	•		•															
JEHCCU 0051 CM1		•	•		•															
JEHCCU 0063 CM1		•	•		•															
JEHCCU 0077 CM1		•	•			•														
JEHCCU 0095 CM1		•	•			•														
JEHCCU 0050 CM1		•	•		▲★															
JEHCCU 0067 CM1		•	•			● ▲ ★ *														
JEHCCU 0100 CM1		•	•			▲★ *														
JEHCCU 0113 CM1		•	•			▲★ *														
JEHCCU 0140 CM1/3		•	•				▲★ *													
JEHSCU 0200 CM1/3	•		•	•			•	• A												
JEHSCU 0250 CM1/3	•		•	•			•	▲ ★ ×	•											
JEHSCU 0300 CM1/3	•		•	•				•	▲ ■ ★×	•										
JEHSCU 0350 CM3	•			•				•	A	•■ ×★										
JEHSCU 0400 CM3	•			•					•		■ ★	• 🛦								
JEHSCU 0500 CM3	•			•						•		ж×								
JEHSCU 0600 CM3	•			•							•		_	• =	A					
JEHSCU 0680 CM3	•			•							•				• = × *	_				
JEHSCU 0800 CM3	•			•								•					▲ ■ ★×	•		
JEHSCU 1000 CM3	•			•										•						●▲ ★×
LT cooling					<1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
JEHCCU 0115 CL1		•	•		•	-	_	-	-		_	-	-							
JEHSCU 0200 CL3	•			•		•														
JEHSCU 0300 CL3	•			•		• =														
JEHSCU 0400 CL3	•			•		~ ^	■ ★	•												
JEHSCU 0500 CL3	•			•			×	• * ×												
JEHSCU 0600 CL3	•			•				*	•											
JEHSCU 0750 CL3	•			•				×	■ ★	•										

JEHCCU-CM1/JEHCCU-CM3



Refrigeration solution for small food retailers

- > Designed specifically for small capacity refrigeration applications in small food stores (eg. in bakeries and butchers), cold rooms, bottle coolers and display cabinets
- Compact and lightweight for even the smallest of city centre locations
- > All components can be accessed, making maintenance quick and
- > Ideal for urban applications: sound proofing and low operating sound levels mean the unit is quiet
- > The optimised compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes
- > Micro channel heat exchanger technology reduces the amount of refrigerant used in the system, lowering environmental impact





Medium Temperature Refrigeration JEHCCU-CM1/CM3							0051 CM1	0063 CM1	0067 CM1	0077 CM1	0095 CM1	0100 CM1	0113 CM1	0140 CM1	0140 CM3
Medium		R-134a	Nom	kW	0,55 (1)	-	0,83 (1)	0,99 (1)	-	1,20 (1)	1,49 (1)			-	
tempera	iture	R-404A*	Nom	kW	-	0,91 (1)		-	1,23 (1)		-	1,50 (1)	1,76 (1)	2,19 (1)	2,22 (1)
		R-407A	Nom	kW	-	0,72 (1)		-	0,97 (1)		-	1,19 (1)	1,49 (1)	1,73 (1)	1,74 (1
		R-407F	Nom	kW	-	0,78 (1)		-	1,03 (1)		-	1,26 (1)	1,55 (1)	1,87 (1)	1,88 (1)
Medium		R-134a	Nom	kW	0,43 (1)	-	0,54 (1)	0,64 (1)	-	0,74 (1)	0,90 (1)			-	,
temperature		R-404A*	Nom	kW	-	0,63 (1)		-	0,76 (1)		-	0,93 (1)	1,10 (1)	1,18 (1)	1,24 (1
		R-407A	Nom	Nom kW		0,54 (1)		-	0,70 (1)		-	0,84 (1)	0,98 (1)	1,11 (1)	1,16 (1
		R-407F	Nom	kW	-	0,53 (1)		-	0,69 (1)	-		0,83 (1)	0,98 (1)	1,07 (1)	1,12 (1
	R-134a	Te -10°C	Declared COP	(COP2)	1,55	-	1,75	1,80	-	1,96	2,05			-	
	R-404A*	Te -10°C	Declared COP	(COP2)	-	1,88		-	1,92		-	1,87	1,95	1,96	2,02
	R-407A	Te -10°C	Declared COP	(COP2)	-	1,39		-	1,45		-	1,50	1,	65	1,58
	R-407F	Te -10°C	Declared COP	(COP2)	-	1,62	-		1,66		-	1,68	1,78	1,95	1,87
	R-134a	Te -10°C	Rated COP (0	OPA)	1,28	-	1,53	1,55	-	1,63	1,65				
•	R-404A*	Te -10°C	Rated COP (0	OPA)	-	1,45	1,61				-	1,61	1,60	1,68	1,80
	R-407A	Te -10°C	Rated COP (0	OPA)	-	1.33		_	1.37		_	1.42	1,52	1.57	1,50
	R-407F	Te -10°C	Rated COP (0	OPA)	-	1,47		-	1,49		-	1,51	1,58	1,75	1,67
	R-134a				1.18	-	1.20	1.21	-	1.30	1.32	,		-	, ,
					-	1.10	,	-	1.18			1.21	1.20	1.26	1,31
-					-	_			, .	-		,		-	1,30
	R-407F				-					-				-	1,32
Unit				mm					607					-	62
				mm		876								1.101	
						420								444	
Unit					4	45 53 54 55						55		58	
				9										-	
					AE4440Y-FZ1A	AE44607-F71C	CAJ4461Y	CA J4476Y			•	CAJ9510Z	CAJ9513Z	CAJ4517Z	TAJ4517
		Charged v	olume										-		
						· · · · · · · · · · · · · · · · · · ·									
		nt		m³/h	1.3	80	3.18	3.79				3.18	4.21	4.	.52
									,	Axial		.,	,	,	-
	rate	Cooling	Nom	m³/h					1.300					2.7	700
Nom.				dBA		29	(2)		28 (2)	29	(2)	28	(2)	34	(2)
					R-134a	R-404A	R-1	34a					R-4		. ,
					-			-					R-4	07A	
					-			-			-				
					1.430.0	_	1.4	30.0		1.4	30.0				
					-									-	
					-			-			-				
		ion		inch			4"					3/8"		-	
													5	/8	
ower supply Phase/Frequency/Voltage Hz/V															3~/50/40
	Medium temperal Medium tempera	Medium temperature Medium temperature R-134a R-404A* R-407A R-407F R-407F R-407F R-134a R-404A* R-407F R-134a R-407F Unit Unit Unit Unit Upe Model Oil Oil Type Piston displacemen Type Air flow rate Nom. Type Type 2 Type 3 GWP Type 2 GWP Type 3 Liquid line connect Suction line connect Suction line connect	Medium	Medium temperature	Medium	Medium	Medium temperature R-134a Nom kW 0,555 (1) - temperature R-404A* Nom kW - 0,91 (1) R-407A Nom kW - 0,72 (1) R-407A Nom kW - 0,72 (1) R-407F Nom kW - 0,72 (1) R-407F Nom kW - 0,73 (1) R-407F Nom kW 0,43 (1) - temperature R-134a Nom kW 0,43 (1) - temperature R-134a Nom kW 0,43 (1) - temperature R-404A* Nom kW - 0,63 (1) R-407F Nom kW - 0,54 (1) R-407F Nom kW - 0,53 (1) R-407F R-407F Nom kW - 0,53 (1) R-407F Te-10°C Declared COP (COP2) R-404A* Te-10°C Declared COP (COP2) R-404A* Te-10°C Declared COP (COP2) R-404A* Te-10°C Rated COP (COP2) R-404A* Te-10°C Rated COP (COPA) R-407F Te-10°C Declared COP (COP3) R-407F Te-10°C Te-10°C Declared COP (COP3) R-407F Te-10°C Declared COP (COP3) R-407F Te-10°C Declared COP (COP3) R-407F Te-10°C T	Medium temperature temperatur	Medium	Medium	Medium Refrigeration Re	Medium Refule Refule	Medium	Medium M	Medium

 $^{(1) \} Refer to \ condition: Outside \ ambient \ temperature = 32^{\circ}C, \ Evaporation \ temperature = -10^{\circ}C \ and \ 10K \ superheat \ (medium \ temperature \ application)$

⁽²⁾ Average sound pressure level is measured at 10m in anechoic room

^{*} R-404A refrigerant is not 2020 F-Gas Compliant



Condensing unit for commercial refrigeration with scroll technology

Refrigeration solution for small food retailers

- > Designed specifically for small capacity refrigeration applications in small food stores (eg. in bakeries and butchers), cold rooms, bottle coolers and display cabinets
- > Compact and lightweight for even the smallest of city centre locations
- > All components can be accessed, making maintenance quick and
- > Ideal for urban applications: sound proofing and low operating sound levels mean the unit is quiet
- > The optimised compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes
- > Micro channel heat exchanger technology reduces the amount of refrigerant used in the system, lowering environmental impact




Medium Temperature	e Refrige	ration		JEHSCU-CM1/CM3	0200 CM1	0250 CM1	0300 CM1	0200 CM3	0250 CM3	0300 CM3	0350 CM3	0360 CM3	0400 CM3	0500 CM3	0600 CM3	0680 CM3	0800 CM3	1000 CM3
Refrigerating capacity	Medium		R-134a	Nom kW	2,05 (1)	2,59 (1)	3,09 (1)	2,17 (1)	2,48 (1)	3,06 (1)	3,48 (1)	3,69 (1)	4,24 (1)	5,24 (1)	6,16 (1)	6,89 (1)	7,95 (1)	10,40
	tempera	ture	R-404A*	Nom kW	3,54 (1)	3,99 (1)	4,92 (1)	3,49 (1)	4,21 (1)	4,89 (1)	5,50 (1)	5,92 (1)	6,70 (1)	8,03 (1)	9,45 (1)	10,15 (1)	12,95 (1)	16,45
			R-407A	Nom kW	3,39 (1)	3,98 (1)	4,65 (1)	3,36 (1)	3,94 (1)	4,54 (1)	-	5,61 (1)	6,57 (1)	8,03 (1)	9,24 (1)	10,35 (1)	12,55 (1)	14,75
			R-407F	Nom kW	3,26 (1)	3,73 (1)	4,50 (1)	3,22 (1)	3,85 (1)	4,45 (1)	-	5,61 (1)	6,62 (1)	7,99 (1)	9,36 (1)	10,40 (1)	12,65 (1)	15,95
Power input	Medium		R-134a	Nom kW	1,11 (1)	1,21 (1)	1,45 (1)	1,03 (1)	1,17 (1)	1,46 (1)	1,68 (1)	1,61 (1)	1,85 (1)	2,30 (1)	2,70 (1)	3,15 (1)	3,74 (1)	4,86 (
	tempera	ture	R-404A*	Nom kW	1,57 (1)	2,00 (1)	2,62 (1)	1,70 (1)	2,04 (1)	2,52 (1)	3,04 (1)	2,88 (1)	3,33 (1)	4,39 (1)	4,92 (1)	5,53 (1)	5,96 (1)	8,62 (
			R-407A	Nom kW	1,60 (1)	1,99 (1)	2,47 (1)	1,63 (1)	2,03 (1)	2,45 (1)	-	2,58 (1)	2,97 (1)	3,93 (1)	4,62 (1)	5,54 (1)	6,24 (1)	8,41 (
			R-407F	Nom kW	1,74 (1)	2,09 (1)	2,66 (1)	1,78 (1)	2,16 (1)	2,71 (1)	-	2,91 (1)	3,21 (1)	4,36 (1)	5,03 (1)	5,98 (1)	6,13 (1)	8,84 (
Seasonal energy		R-134a	Te -10°C					-				2,29	-	2,69	2,63	2,57	2,92	2,88
performance ratio		R-404A*	Te -10°C					-			2,61	3,48	2,77	2,64	2,72	2,65	2,90	2,57
SEPR		R-407A	Te -10°C					-				3,44	3,09	2,81	2,75	2,65	2,88	2,35
		R-407F	Te -10°C					-				3,2	2,83	2,60	2,69	2,59	2,83	2,53
Annual electricity	_0_	R-134a	Te -10°C	kWh/a					-					11.969	14.381	16.491	16.741	22.22
consumption Q	•	R-404A*	Te -10°C	kWh/a				-			12.939	10.448	14.881	18.673	21.344	23.536	27.407	39.37
	-	R-407A	Te -10°C	kWh/a	h/a - 1				10.033	13.054	17.546	20.622	24.031	26.747	38.51			
		R-407F	Te -10°C	kWh/a				-				10.766	14.365	18.883	21.395	_	27.475	
Parameters at full		R-134a		Declared COP (COP2)	2.15	2,54	2.50	2,55	2	52	2.46	2.8	2,83			-		1
load and ambient		R-404A*		Declared COP (COP2)	2,65	2,54	2,24	2,44	2,41	2,26		2,66	2,03			_		
temp. 25℃	•	R-407A		Declared COP (COP2)	2,55	2,38	2,21	2,50	2,32	2,20	_	2,72						
		R-407F		Declared COP (COP2)	2,43	2,31	2,16	2,35	2,25	2,10	-	2,72						
Parameters at full load		R-4071		Rated COP (COPA)	1,85	2,14	2,10	2,12	2,23	2,10	2,08	2,29	2,29	2	28	2,19	2,13	2,14
and ambient temp.		R-404A*		Rated COP (COPA)	2,25	2,14	1,88	2,12	2,13	1,94		2,29	2,29		1,92		2,13	_
32°C (Point A)	•	R-407A									1,81		-	1,83		1,84	-	1,91
52 6 (1 5111671)				Rated COP (COPA)	2,13	2,01	1,89	2,07	1,95	1,86		2,17	2,21	2,04	2,00	1,87	2,01	1,75
D	_	R-407F		Rated COP (COPA)	1,88	1,79	1,69	1,81	1,79	1,65	- 1.52	1,93	2,06	1,83	1,86	1,74	2,06	1,80
Parameters at full load and ambient		R-134a		Declared COP (COP3)	1,35		53		1,57		1,52	1,6	1,55	1,56	1,59	1,53		,52
temp. 43°C	•	R-404A*		Declared COP (COP3)	1,53	1,33	1,	.25	1,36	1,28	1,11	1,31	1,28	1,15	1,27	1,22	1,47	1,18
temp. 45 C		R-407A		Declared COP (COP3)		-		1,48	1,45	1,38	-	1,48	1,43	1,39	1,43	-	1,38	-
		R-407F		Declared COP (COP3)							-						1,52	<u> </u>
Dimensions	Unit		Height	mm				662				872		8				727
			Width	mm				1.101				1.353					348	
			Depth	mm		1	1	444	1	1		575		5		1	_	541
Weight	Unit			kg	70	72	74	70	72		74	112	119	123	125	126	2	18
Compressor	Туре										Scroll co							
	Model				ZB15KQE-PFJ	ZB19KQE-PFJ	ZB21KQE-PFJ	ZB15KQE-TFD	ZB19KQE-TFD	ZB21KQE-TFD	ZB26KQE-TFD	ZB26KQE-TFD		_		_		ZB76KCE-T
	Oil		Charged	volume I				-				1,5	1,36	2,07	1,89	1,80	2,5	3,2
	Oil Type										nd 32-3M/							
	Piston di	splacemer	nt	m³/h	5,90	6,80	8,60	5,90	6,80	8,60	9,90	9,90	11,40	14,40	17,10	18,80	22,10	29,10
Fan	Type										Ax	ial						
	Air flow	rate	Cooling	Nom m³/h				2.700				4.250					8.5	500
Sound pressure level	Nom.			dBA	33 (2)	34 (2)	36 (2)	33 (2)	34 (2)	36 (2)	39 (2)	37 (2)	37 (2)	38 (2)	40	(2)	43	3 (2)
Refrigerant	Type										R-1	34a						
	Type 2										R-4	04A						
	Type 3						R-4	-07A			-				R-407A			
	Type 4						R-4	107F			-				R-407F			
	GWP										1.4	30						
	GWP Typ	ne 2							21,6									
	GWP Typ				2.107 -						2.107							
	GWP Type 4					1.825						1.825						
Piping connections	Liquid line connection inch											3/4"				3,	/4"	
											1/2" 7/8" 1 1/8" 3/8							
	Suction	ine connec	Suction line connection inch Phase/Frequency/Voltage Hz/V									3~/50/400						

⁽²⁾ Average sound pressure level is measured at 10m in anechoic room

^{*}R-404A refrigerant is not 2020 F-Gas Compliant
** Also compatible with refrigerants R-448A and R-449A. For more information consult RefrigXpress

Blue cells contain preliminary data

JEHCCU-CL1/JEHSCU-CL3



Refrigeration solution for small food retailers

- > Designed specifically for small capacity refrigeration applications in small food stores (eg. in bakeries and butchers), cold rooms, bottle coolers and display cabinets
- > Compact and lightweight for even the smallest of city centre locations
- > All components can be accessed, making maintenance quick and easy
- > Ideal for urban applications: sound proofing and low operating sound levels mean the unit is quiet
- > The optimised compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes
- > Micro channel heat exchanger technology reduces the amount of refrigerant used in the system, lowering environmental impact





Low Temperature Ref	frigeratio	on	JEI	ICCU-CL1/JEI	ISCU-CL3	JEHCCU0115CL1	JEHSCU0200CL3	JEHSCU0300CL3	JEHSCU0400CL3	JEHSCU0500CL3	JEHSCU0600CL3	JEHSCU0750CL3	JEHSCU0950CL3-EVI
Refrigerating capacity	Low tem	perature	R-404A*	Nom	kW	0,69 (1)	1,42 (1)	1,98 (1)	2,91 (1)	3,53 (1)	4,13 (1)	5,29 (1)	5,9 (1)
			R-407A	Nom	kW	-	1,16 (1)	1,51 (1)	2,29 (1)	2,77 (1)	3,31 (1)	4,29 (1)	4,96 (1)
Power input	Low tem	perature	R-404A*	Nom	kW	0,72 (1)	1,46 (1)	1,81 (1)	2,38 (1)	3,10 (1)	3,69 (1)	3,88 (1)	4,35 (1)
			R-407A	Nom	kW	-	1,31 (1)	1,77 (1)	2,33 (1)	2,85 (1)	3,57 (1)	4,17 (1)	3,94 (1)
Seasonal energy		R-404A*	Te -35°C				-		1,88	1,79	1,80	1,82	1,79
performance ratio SEPR		R-407A	Te -35°C				=		1,67 1,52			1,51	1,76
Annual electricity		R-404A*	Te -35°C		kWh/a		-		11.555	14.732	17.107	21.649	24.503
consumption Q		R-407A	Te -35°C		kWh/a		=		10.212	12.364	16.220	21.146	20.958
Parameters at full load and	_0_	R-404A*	Te -35°C	Declared CO	(COP2)	1,11	1,16	1,40	_				1,58
ambient temp. 25°C		R-407A	Te -35°C	Declared CO	(COP2)	-	1,12	1,08			-		1,51
Parameters at full load and ambient		R-404A*	Te -35°C	Rated COP	COPA)	0,96	0,97	1,09	1,22	1,14	1,06	1,36	1,36
temp. 32°C (Point A)	•	R-407A	Te -35°C	Rated COP	COPA)		0,89	0,85	0,98	0,97	0,93	1,03	1,26
Parameters at full load and		R-404A*	Te -35°C	Declared CO		0,69	0,60	0,70	0,86	0,79	0,64	0,98	1,06
ambient temp. 43°C		R-407A	Te -35°C	Declared CO		-	0,55	-	0.67	0,66	0,64	0,73	-
Dimensions	Unit		Height	mm		607	662		0,07	872	0,0 .	1.727	1.727
Dimensions	01		Width		mm	876	1.101			1.353		1.348	1.348
			Depth		mm	420		44		575		605	605
Weight	Unit				kg	55	76	77	13	32	133	203	200
Compressor	Type					Reciprocating compressor			:	Scroll compres	sor		
	Model					CAJ2446Z	ZF06K4E-TFD	ZF09K4E-TFD	ZF13K4E-TFD	ZF15K4E-TFD	ZF18K4E-TFD	ZF25K5E-TFD	ZF18KVE-TFD-EVI
	Oil		Charged v	olume	- 1	0,9		-		1,	90		1,90
	Oil Type					Uniqema Emkarate RL32CF	Polyes	ter oil (Copeland U	ltra 22 CC, 32 CC a	nd 32-3MAF, Mob	il EAL™ Arctic 22 C	C, Uniqem Emkara	ite RL32CF
	Piston d	isplacemer	nt		m³/h	4,55	5,90	8,00	11,80	14,50	17,10	21,40	17,1
Fan	Туре								Α	xial			
	Air flow	rate	Cooling	Nom	m³/h	1.300	2.7	700		-		5.750	5.870
Sound pressure level	Nom.				dBA	31 (2)	32 (2)	33 (2)	37 (2)	39 (2)	41	(2)	37
Refrigerant	Туре								R-4	104A			
	Type 2					-				R-407A			
	GWP								3.921,6				
	GWP Type 2					-			2.107,0				
Piping connections	,,				inch		3/8"				2"	7/8"	
	Suction	line conne	tion		inch	1/2"	3/4" 7/8" 1 1/8"				1 1/8"	1/2"	
Power supply	Phase/Frequency/Voltage Hz/					1~/50/230	~/50/230 3~/50/400						

(1) SRG 20°C, Ta=32°C, Te=-35°C (2) Average sound pressure level is measured at 10m in anechoic room

^{*} R-404A refrigerant is not 2020 F-Gas Compliant

Blue cells contain preliminary data



LUU, LLU

Condensing unit for outdoor installation with hermetic compressors

General features:

- > Capacity for MT cooling: 0,9 kW to 26,7 kW
- > Capacity for LT cooling: 0,6 kW to 12 kW
- > Ambient temperature range : 25°C +43°C
- R134A a, R 449A, R448A, R452A R407F, depending on the compressor
- > Compressors:
- LUU* : Tecumseh
- LUA* : Embraco
- LUE* : Scroll
- LUF* : Digital Scroll Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: -35°C Evp. Temperature: -35°C



Compact air cooled condensing unit floor mounting, low noise, with hermetic compressors. Designed specifically for small capacity refrigeration applications in small food stores (eg. in bakeries and butchers), cold rooms, bottle coolers and display cabinets. All components can be accessed, allowing for quick and easy maintenance.

The optimized compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes.



Standard characteristics:

- > Hermetic compressor with integral protection
- > Dual HP/LP fixed switch with auto reset
- > Liquid line filter dryer, liquid line sight glass
- > Curved condenser with 6-pole fan motor
- > Liquid receiver with safety pressure relief valve for PED units (depending on the model & PED class)
- Electrical box with capacity controller (only for digital scroll)
- > Crankcase heater (only scroll type)

Normal cooling

Condensing unit		LUUMF	50AV3	100AV3	122AV3	120AW1	150AW1	200AW1	250AW1	255AW1
Refrigeration capacity	-10° C	W	930	1094	2130	2130	2720	3010	3920	4230
Power input		kW	0,68	1,4	1,4	1,45	2,08	2,18	2,97	2,99
COP 32°C (1)			2,02	2,23	2,15	2,15	1,95	1,88	2,00	2,17
COP 25°C (1)			1,70	1,86	1,81	1,81	1,65	1,60	1,71	1,85
COP 43°C (1)			1,26	1,37	1,34	1,34	1,23	1,19	1,29	1,40
Dimensions Unit	Height	mm		4	85			586		717
	Width	mm		7-	45			852		1006
	Depth	mm		5	15			600		682
Condenser air flow		m³/h	1000	1460	1460	1460	2600	2600	2400	3950
Compressor						Hermetic	Tecumseh			
Refrigerant		Type/GWP				R404A	A / 3922			
Power supply		V/~/ Hz		230/1/50				400/3/50		

Deep freezing

Condensing unit		LUULF	120AV3	170AV3	300AW1						
Refrigeration capac	ity -35° C	W	620	870	1480						
Power input		kW	1,08	1,35	2,38						
COP 32°C (1)			1,35	1,11	1,14						
COP 25°C (1)			0,96	0,95	0,97						
COP 43°C (1)			0,73	0,73	0,73						
Dimensions Unit	Height	mm	4	85	586						
	Width	mm	7-	45	852						
	Depth	mm	5	15	600						
Condenser air flow		m³/h	1000	1460	2600						
Compressor				Hermetic Tecumseh							
Refrigerant		Type/GWP	R404A / 3922								
Power supply V/~/ Hz			230,	230/1/50 400/3/50							

Other refrigerants, compressors and options availibal on request (1) Nominal operating conditions according to Ecodesign EN 13215: Ambient temperature 32°C/25°C/43°C, Evaporation temperature -10°C -35°C, 20°C suction gas temperature, Sub cooling 0K; (2) Not existing at the moment

* Note: Depending on model, selection from Selection software based on R404A, R134a, R407F. Some models also available with R449A

LU* Condesing units
LL* Low noise condesing units
Compressor:
LUU* Tecumseh
LUA* Embraco
LUE* Scroll

Digital Scroll

Condensing unit for outdoor installation with semi hermetic compressors

General features:

- > Capacity for MT cooling: 1,37 kW to 72,3 kW
- > Capacity for LT cooling: 0,77 kW to 35,2 kW
- > Ambient temperature range : 25°C +43°C
- > R134A a, R 449A, R448A, R452A R407F, R 407A
- > Compressors:
 - LUB* : Bitzer
- LUD* : Dorin
- LUR* : Frascold
- LUC* : Copeland stream
- > Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

General Description:

Compact air cooled condensing unit floor mounting, low noise, with semi hermetic compressors.

Designed specifically for small capacity refrigeration applications in small and medium sized food stores (e.g. in bakeries and butchers), cold rooms, bottle coolers and display cabinets. All components can be accessed, allowing for quick and easy maintenance. The optimized compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes.



Standard characteristics:

- > Semi-hermetic compressors
- > Crankcase heater Kriwan
- > Curved condenser with 6-pole fan motor
- > Electrical box with terminal strip
- > Liquid receiver with safety pressure relief valve for PED units
- > Liquid line filter dryer, liquid line sight glass
- > Dual HP/LP adjustable switch with auto reset
- > Suction vibration eliminator
- > Frequency driver (only with Inverter option)
- > Bitzer Varispeed compressor (only for Inverter option)
- > Electrical box with running processor (only for Inverter)

Normal cooling

_														
Condensing unit		LUBMF-AW1	100	120	200	250	255	300	350	450	600	750	800	MOO
Refrigeration capacity	/ -10° C	W	1.850	2.380	3.400	4.210	4.560	5.950	7.160	9.510	11.970	13.950	16.910	21.180
Power input		kW	1,65	1,65	2,50	3,17	3,19	4,03	4,93	6,34	7,61	8,69	8,61	12,45
COP 32°C (1)			2,45	2,26	2,06	2,14	2,37	2,68	2,35	2,44	2,54	2,47	2,50	2,45
COP 25°C (1)			2,01	1,87	1,72	1,76	1,96	2,25	1,97	2,05	2,12	2,07	2,10	2,07
COP 43°C (1)			1,45	1,36	1,25	1,27	1,41	1,68	1,48	1,53	1,59	1,55	1,57	1,54
SEPR ⁽¹⁾					-			3,25	2,80	2,95	3,09	2,97	3,01	2,90
Annual Electricity Consu	mption ⁽¹⁾	Kwh/a			-			11.249	15.707	19.782	23.791	28.907	34.556	44.904
Dimensions Unit	Height	mm	48	85	58	36	7	17			90	60		
	Width	mm	74	45	8.	52	1.0	06	1.3	60		1.630		2.030
	Depth	mm	5	15	60	00	6	82	9.	31		1.1	20	
Condenser air flow		m³/h	1.460	1.460	2.600	2.400	3.950	3.640	6.530	6.220	9.090	9.090	8.230	11.100
Compressor		Ī						Semi-Hern	netic Bitzer					
Refrigerant		Type/GWP						R404A	/ 3922					
Power supply		V/~/ Hz						400/	3~/50					

Deep freezing

Condensing unit		LUBLF-AW1	170	200	455	500	650	800	M00	M25				
Refrigeration capacity	y -35° C	W	670	1130	3020	3830	5510	6430	6990	8640				
Power input		kW	0,93	1,75	3,82	5,24	7,02	8,21	10,83	12,25				
OP 32°C (1)			1,14	1,28	1,45	1,51	1,42	1,47	1,51	1,50				
COP 25°C (1)	COP 25°C (1)		0,98	1,10	1,25	1,30	1,23	1,27	1,30	1,30				
COP 43°C (1)			0,75	0,84	0,98	1,02	0,95	0,96	1,01	1,03				
SEPR ⁽¹⁾					-		1,66	1,69	1,73	1,75				
Annual Electricity Consu	umption ⁽¹⁾	Kwh/a					24730	28369	30158	36899				
Dimensions Unit	Height	mm	4	85	7	17		9	60					
	Width	mm	74	45	10	06	13	60	16	30				
	Depth	mm	5	15	68	32	9:	31	1120					
Condenser air flow	•	m³/h	1000	1460	3640	3640	6220	6220	6480	9090				
Compressor			Semi-Hermetic Bitzer											
Refrigerant		Type/GWP				R404A	A / 3922							
Power supply		V/~/ Hz				400/	3~/50							

Other refrigerants, compressors and options availibal on request (1) Nominal operating conditions according to Ecodesign EN 13215: Ambient temperature 32°C/25°C/43°C, Evaporation temperature -10°C -35°C, 20°C suction gas temperature, Sub cooling 0K

LU*: Condensing units
LL*: Low noise condensing units
Compressor:
LUB*: Bitzer
LUD*: Dorin
LUR*: Frascold
LUC*: Copeland Stream

^{*} Note: Depending on model, selection from Selection software based on R404A, R134a, R407F. Some models also available with R449A

LTT, LTP, LTL

Twin condensing unit for outdoor installation with twin-hermetic and semi hermetic compressors

General features:

- > Capacity for MT cooling: 8,5 kW to 26 kW
- > Capacity for LT cooling: 7,5 kW to 12 kW
- > Ambient temperature range : 25°C +43°C
- > R134A a, R 449A, R448A, R452A R407F
- > Compressors:
- LTT*: Twin Scroll
- LTP*: Digital Scroll
- LTL* : Semi hermetic Bitzer
- > Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

General Description:

Compact air cooled condensing unit floor mounting, low noise, with hermetic compressors. Designed specifically for small capacity refrigeration applications in small food stores (eg. in bakeries and butchers), cold rooms, bottle coolers and display cabinets. All components can be accessed, making maintenance quick and easy.

The optimized compressor range and increased condenser surface deliver high levels of energy efficiency and reliability is ensured by using high quality components and production processes.



Standard characteristics:

- > Two compressors parallel connected
- > Level control oil system
- > Curved condenser with 6-pole fan motor
- > Electrical box with terminal strip
- > Liquid receiver with safety pressure relief valve for PED units
- > Liquid line filter dryer, liquid line sight glass
- > Dual HP/LP adjustable switch with auto reset
- > Suction vibration eliminator
- > Electrical box with Running processor (only for Inverter)

Normal cooling

Condensing unit		LTTMF-AW1	046	060	070	080	082	100	120	150		
Refrigeration capacity	-10° C	W	8.130	10.085	11.846	13.097	14.152	17.620	21.022	23.714		
Power input		kW	5,97	7,13	8,29	9,45	9,68	11,94	13,44	15,68		
COP/EER (1)			1,94	1,92	1,97	1,90	2,20	2,06	2,20	2,11		
SEPR ⁽¹⁾			3,57	3,68	3,80	3,75	3,96	3,85	3,99	4,18		
Annual Electricity Consu	mption ⁽¹⁾	Kwh/a	14017	16.859	19.168	21.454	21.944	28.100	36.536	30.916		
Dimensions Unit	Height	mm				1.4	-80					
	Width	mm		1.6	80			2.4	105			
	Depth	mm				75	50					
Condenser air flow		m³/h	7.800	7.800	7.300	7.300	15.600	15.600	15.600	14.600		
Compressor						Twin Scroll	- Copeland					
Refrigerant		Type/GWP				R404A	/ 3922					
Power supply		V/~/ Hz	400/3~/50									

Deep freezing

Condensing unit		LTTLF-AW1	100	120	150	200	260	300					
Refrigeration capacity	/ -35° C	W	6.512	7.709	9.644	13.009	16.307	18.964					
Power input		kW	12,97	13,97	14,41	19,58	23,96	26,96					
COP/EER (1)			0,98	0,97	1,16	1,17	1,19	1,12					
SEPR ⁽¹⁾			1,85	1,93	2,05	2,03	2,08	2,05					
Annual Electricity Consu	umption ⁽¹⁾	Kwh/a	26.307	29.722	37.990	47.775	58.560	68.836					
Dimensions Unit	Height	mm			14	80							
	Width	mm		1680			2405						
	Depth	mm			7:	50							
Condenser air flow	·	m³/h	7.600	7.300	7.300	15.600	14.600	14.600					
Compressor					Twin Scrol	l - Copeland							
Refrigerant		Type/GWP	R404A / 3922										
Power supply		V/~/ Hz	400/3~/50										

Multi compressor condensing unit with scroll/digital scroll compressors

General features:

- > Capacity for MT cooling: 10,5 kW to 102 kW
- > Capacity for LT cooling: 7,5 kW to 48,5 kW
- > Ambient temperature range : 25°C +43°C
- > R134A a, R 449A, R448A, R452A R407F
- Copeland scroll and digital scroll compressors
 Other types, brands and capacities are possible on request
- > Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

Standard configuration:

Basic Frame Version:

Basic frame made from pre-painted steel sheet, with vertical condenser placed on 1 or 2 sides of the unit and fans (2, 3, 4, or 5) placed on frame top covering sheet

The compressors are installed in a soundproof compartment separate from the condenser side, but allowing ventilation.

The compartment is simple soundproofing insulated (SMP)

Basic Refrigerating System:

The compressors (3 or 4) are connected in parallel, with one suction and discharge header. Each compressor is fitted with shut-off valves on suction line and discharge line.

The compressors are fixed to the frame through rubber anti-vibration supports.

The oil equalization system is composed of an oil separator and an equalization header, which are mounted on the compressor oil sight glass connection

According to the number of compressors fitted, there are one or two oil level indicator/s, fitted onto the equalization header.

The refrigerating system is equipped with liquid receivers, if there is more than one receiver, the installation is made in parallel with a safety valve, a dehydration cartridge filter, interchangeable, liquid level alarm, liquid sight glass and shut-off valves. On suction line there is a mechanical cartridge filter, interchangeable.



The refrigeration system is fitted with:

- General high pressure switch, adjustable and autoresetting
- General low pressure switch, adjustable and autoresetting
- Emergency low pressure switch, adjustable and autoresetting
- > Low pressure switches for each compressor emergency, adjustable and autoresetting
- Low pressure probe, placed on suction header for capacity control
- > High pressure gauge
- > Low pressure gauge

Standard electrical panel:

Standard power distribution Disconnecting switch

Compressors protection, with overload cut-out motor protector; fuses for fans protection, thermo-contacts for each single fan.

Auxiliary circuit 230 volt through transformer 400V/230V

Electronic card XC440C

Four alarm signals: emergency (button + lamp, fans block, high pressure switch block, low pressure switch block.

Electronic speed regulator for condenser fan with pressure probe for three phase fans and with temperature probe for mono phase fans + bypass The electrical panel is placed horizontally on the top front side of the unit, inside the panel sheets for frame 1, 2 and 3; greed, ventilation fan and double door for frames 4, 5, 6 and 7.

LHB, LHD, LHR and LHC

Multi compressor condensing unit with semi hermetic compressors

General features:

- > Capacity for MT cooling: 48 kW to 150 kW
- > Capacity for LT cooling: 20 kW to 85 kW
- > Ambient temperature range : 25°C +43°C
- > R134A a, R 449A, R448A, R452A R407F
- > Compressors:
- LHB*: Bitzer
- LHD* : Dorin
- LHR* : Frascold
- LHC* : Stream

Other types, brands and capacities are possible on request

> Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

General description:

Basic Frame Version:

Basic frame made from folded and painted steel sheet, screwed with bolts to make a basic structure to fix the components on it.

Basic Refrigerating System:

The compressors (3 or 4) are connected in parallel, with only one suction and discharge header. Each compressor is fitted with shut-off valves on suction line and discharge line.

The compressors are fixed to the frame through rubber anti-vibration supports.

Compressors used for low temperature are complete with fan heads.

The oil equalization system is composed of an oil separator and an equalization header, which are mounted on the compressor oil sight glass connection

According to the number of compressors fitted, there is one or two oil level indicator/s, fitted onto the equalization header.

The refrigerating system is equipped with liquid receivers, if there is more than one receiver, the installation is made in parallel with a safety valve, a dehydration cartridge filter, interchangeable, liquid level alarm, liquid sight glass and shut-off valves. On suction line there is a mechanical cartridge filter, interchangeable.



The refrigeration system is fitted with:

- General high pressure switch, adjustable and autoresetting
- General low pressure switch, adjustable and autoresetting
- > Oil pressure switch for each compressor
- > Emergency low pressure switch, adjustable and autoresetting
- Low pressure switches for each compressor emergency, adjustable and autoresetting
- > Electronic speed regulator for condenser fan with pressure probe for three phase fans and with temperature probe for mono phase fans + bypass
- Low pressure probe, placed on suction header for capacity control
- > High pressure gauge
- > Low pressure gauge

Electrical panel:

Standard power distribution

Disconnecting switch

Compressors protection, with overload cut-out motor protector; fuses for fans protection, thermos contacts for each single fan


Auxiliary circuit 230 volt through transformer 400V/230V

Electronic card XC440C

IP55 with greed and ventilation fan

On the door there is the electronic card and 4 lamps: emergency (button + lamp), fans block, high pressure switch block, low pressure

Switch block, and selector for on/off compressors







Why choose ZEAS?

Whether it is restaurants, supermarkets or event halls – Zeas from Daikin is as individual as the requirements of the industries where it is used.

High energy efficiency

- Daikin DC inverter scroll compressor with economizer technology
- > DC inverter fan technology
- > Eco-design compliant

Reliable operation

- Zeas condensing units are rigorously tested on the assembly line
- > Proven inverter scroll technology
- > Proven onboard innovating economizer technology
- > Anti-corrosion treatment on the housing ensures long life even in extreme conditions

> Lower energy bills

The use of Daikin proven DC technology results in lower energy bill compared to the use of standard ON/OFF units and even other capacity controller refrigeration units

> Our units are future proof

Combining Daikin innovating economizer technology with in house DC technology results in very high efficient units allowing us to outperformed the most severe eco-design minimum performance for the coming decades

BENEFITS

BENEFITS

> Optimal food conservation

Accurate temperature and humidity control can be easily suited to the requirements for different foods and beverages resulting in less of precious products

Longer lifetime expectation of our compressor

Less thermal stress on our bearings and motor windings due to the implementation of Daikin High quality DC technology in our compressor

Longer lifetime expectations of our units

The use of our innovating economizer technology in our units guarantee that our the compressor always operates within his operating envelop even in the most harvest conditions: excessive superheat at the inlet of the compressor resulting from improper quality of installation on the refrigerated cabinets side

No leaks

Each new Daikin designed unit is put on a vibration plate in the factory to be sure that no leak and component damage can occur during transport. Even further, in the assemble line the Zeas unit undergo several leak test

No "dead on arrival"

ALL units leaving the factory, have already run at the end of the assembly line

Lower installation cost

Due to the use of the onboard economizer technology and the use of the correct low GWP refrigerant we only required the use of smaller pipes compared to other traditional systems, thus also lowered the refrigerant charge of the system



Small foot print and low weight

- > Extremely compact and space-saving design
- > Easy to install, even in the smallest spaces
- > Indoor installation possible
- > Best surface to capacity ration on the market
- > Low weight thanks to compact design

> Only light weight supporting structures are required

- No installation restrictions anymore
 Our mini Zeas due to his compact design, light weight and very silent
- No special crane are required
 The ZEAS units are so compact that it can fit in an elevator

Peace of mind

- > Quiet operation, unobtrusive for customers and neighbours
 - High grade sound on panels and compressors
 - Condenser fans designed to limit the noise
- 4 low noise operation settings including night mode
- > Wide temperature range allows multiple cabinet, freezer and cold room combinations

Intelligent control

- > Unit can be connected to third party monitoring system
- > Remote control of target evaporation temperature, reset errors and other functions
- Refrigeration unit can be controlled remotely through a power full interface

BENEFITS

BENEFITS

Happy neighbours and no installation restrictions anymore

The focus on sound criteria during the design of the units results in the mos silent unit(s) of the market (till 25 dB(A) @ 10 m free field conditions)

BENEFITS


> Quick installation and commissioning

Advanced software solution for easy system configuration and

> Peace of mind

Easy monitoring of ZEAS unit by third party Building Management System: through the use of our Modbus interface

ZEAS, the smart choice for medium and low temperature refrigeration




Why R410A?

ZEAS-systems.

R410A is a lower GWP refrigerant (less than 2500) than R404A and is fully F-gas compliant. It's future proof: it can be used even after 2030!


Use of refrigerant in refrigeration system with a refrigeration lower than 40 $kW\,$



Contributes to reducing installation cost and refrigerant charge

R410A is a high pressure refrigerant which for the same swept volume can deliver much more refrigeration capacity than standard mid pressure and low pressure refrigerants.

Delivered capacity per used refrigerant




This means that for the same delivered refrigeration capacity we can use smaller main and linecomponents, thus reducing the installation cost and the amount of refrigerant charge in the system!

For a capacity of 8,4 kW (Te = -10°C / Tamb = 32°C)

Refrigerant	Suction piping diameter
R134a	1 1/8"
R407A	7/8"
R407F	7/8"
R448A	7/8"
R449A	7/8"
R450A	1 1/4"
R410A	3/4"
CO2	1/2"

Refrigerant charge per used refrigerant



R410A is also:

- > an easy to handle, common used refrigerant in the air conditioning world, therefore it is easy to find an installer which can work with this refrigerant, compared to CO₂, Ammonia and Propane.
- > an A1 refrigerant, therefore no special safety measurements are required.

Mini-ZEAS condensing unit for commercial refrigeration with scroll technology

Refrigeration solution for small food retailers

- Inverter technology guarantees optimal food conservation by ensuring an accurate temperature and humidity control
- > The economized scroll contributes to a longer lifetime expectation of the refrigeration equipment and less maintenance requirement
- > The use of R-410A refrigerant allows the use of smaller pipping diameters, thus reducing the refrigerant content in the system helping to lower our CO2 footprint . R-410A is fully compliant with the latest F-Gas regulation and can be still used after 2020 and beyond
- The DC economized compressor improves drastically the efficiency of the unit, thus helps lowering the energy bill!
- > Lowest sound level in the market down to 31 dBA. Sound level can be even further reduced thanks to the low noise modes
- > The weight of the unit is very low, therefore the unit can even be mounted on the wall
- > Up to 75% smaller than equivalent products in the market, ideal for those places where space is limited
- > Advanced software solution for easy system configuration and commissioning







Daikin technology increases the love for German Gourmet

DAIKIN's new Mini-ZEAS condensing unit is ensuring constant refrigeration in storage and production areas at the newly refurbished butcher shop, in mid west Germany. The key to maintaining the quality of the shop's fresh meat and deli products is to store them at constant temperatures, which is also legislatively required to be quality controlled at all times. DAIKIN's new Mini-ZEAS condensing unit, which is specially designed for small-scale commercial refrigeration applications, ensures exactly that. **Fleischeslust, Bensheim, Germany.**

Medium Temperature	e Refrigerati	on		LRMEQ-BY1	3	4
Connectable capacity	Minimum~/	Maximum		%	50~	-100
Refrigerating capacity	Medium temp.	Nom.		kW	5.90 (1)	8.40 (1)
Power input	Medium temp.	Nom.		kW	2.53 (1)	3.65 (1)
COP	Medium temp.	Nom.			2.33 (1)	2.30 (1)
Seasonal energy performance ratio SEPR	R-410A	Te -10°C			4.17	4.08
Annual electricity consumption Q	R-410A	Te -10°C		kWh/a	8,698	12,651
Parameters at full load and ambient temp. 32°C (Point A)	R-410A	Te -10°C	Rated COP (COPA)	2.33	2.30
Parameters at full load and ambient temp. 43°C	R-410A	Te -10°C	Declared CO	P (COP3)	1.51	1.48
Dimensions	Unit	HeightxWi	idthxDepth	mm	1,345x	900x320
Weight	Unit			kg	1	26
Heat exchanger	Туре				Cross	fin coil
Compressor	Type				Hermetically seale	d scroll compressor
	Starting me	thod			Direct on line (inverter driven)
Fan	Туре				Prop	peller
	Quantity					2
	Air flow rate	Cooling	Nom.	m³/min	1	06
Fan motor	Output			W	7	70
	Drive				Direc	t drive
Sound pressure level	Nom.			dBA	51	(2)
Piping connections	Liquid	OD		mm	9,	52
	Gas	OD		mm	1!	9.1
Refrigerant	Type/GWP				R-410A	/2,087.5
	Charge			kg/TCO2Eq	4.50	/9.39
	Control				Electronic ex	pansion valve
Power supply	Phase/Frequ	uency/Volta	ge	Hz/V	3N~/50	/380-415

LREQ-BY1



ZEAS condensing unit for commercial refrigeration with scroll technology

Refrigeration solution for medium to large capacity applications featuring proven VRV technology


- > One model for all applications from -45°C to 10°C evaporating temperature
- > Perfect solution for all cooling and freezing applications with variable load conditions and high energy efficiency requirements. In particular used in supermarkets, cold storage, blast coolers and freezers etc.
- DC inverter scroll compressor with economiser function results in high energy efficiency and reliable performance
- > Reduced CO2 emissions thanks to the use of R-410A refrigerant and low energy consumption
- > Factory tested and pre-programmed for quick and easy installation and commissioning
- > VRV (Variable Refrigerant Volume) technology for flexible application range
- > Increased installation flexibility thanks to limited dimensions
- > Low sound level including "night mode" operation
- > For small freezing capacity, single ZEAS units can be connected to a booster unit
- > Dedicated unit to allow multi combination of 2 x 15 HP or 2 x 20 HP resulting in less pipework or installation time




			L	REQ-BY1	5	6	8	10	12	15	20		
Refrigerating capacity	Low temperatu	e Nom.		kW	5,51 (1)	6,51 (1)	8,33 (1)	10,0 (1)	10,7 (1)	13,9 (1)	15,4 (1)		
	Medium temperatu	e Nom.		kW	12,5 (2)	15,2 (2)	19,8 (2)	23,8 (2)	26,5 (2)	33,9 (2)	37,9 (2)		
Power input	Low temperatu	e Nom.		kW	4,65 (1)	5,88 (1)	7,72 (1)	9,27 (1)	9,89 (1)	12,8 (1)	14,1 (1)		
	Medium temperatu	e Nom.		kW	5,10 (2)	6,56 (2)	8,76 (2)	10,6 (2)	12,0 (2)	15,2 (2)	17,0 (2)		
easonal energy	R-4	0A Te -10°C			3,86	3,79	3,64	3,42	3,51	3,38	3,23		
erformance ratio SEPR	~	Te -35°C			1,80	1,77	1,84	1,88	1,80	1,70	1,70		
Annual electricity	R-4	0A Te-10°C		kWh/a	19.907	24.681	33.483	42.794	46.377	61.683	72.030		
onsumption Q	•	Te -35°C		kWh/a	22.805	27.453	33.817	39.747	44.363	61.090	67.325		
arameters at full load and ambient	R-4		Rated COP (2,45	2,32	2,26	2,25	2,21 2,23				
emp. 32°C (Point A)	•	Te -35°C	Rated COP (1,18	1,11	2,20	1,08			09		
Parameters at full load and	R-4		Declared COP		1,54	1,57	1,40	1,46	1,47	1,46	1,51		
mbient temp. 43°C	•	Te -35°C	Declared COP		0,76	0,74	0,68	0,70		.71	0,74		
Dimensions	Unit	Height	Decidica coi	mm	0,76	0,74	0,00	1.680	U	./1	0,74		
AITHERISIONS	Offic	Width		mm		35		930		1.	240		
		Depth			0	33				1.2	240		
V-:	Unit	Depth		mm			1	765					
Veight				kg	- 1	56		242		331	337		
leat exchanger	Туре							Cross fin coil					
Compressor	Туре			14/			_	ally sealed scroll o	· ·				
	Output			W	2.600	3.200	2.100	3.000	3.400	2.600	3.400		
	Piston displac	ement		m³/h	11,18	13,85	19,68	23,36	25,27	32,24	35,8		
	Speed			rpm	5.280	6.540	4.320	6.060 on line (inverter	6.960	5.280	6.960		
	Starting meth	od											
Compressor 2	Output			W		-			3.600				
	Speed			rpm		-			2.900				
Compressor 3	Output			W			-				500		
	Speed			rpm			-			2.9	900		
an	Туре							Propeller fan					
	Quantity				1					:	2		
	Air flow rate	Cooling	Nom.	m³/min	95	102	171	179	191	230	240		
an motor	Output			W	3	50		750		350	750		
	Drive							Direct drive					
an motor 2	Output			W			-			350	750		
ound pressure level	Nom.			dBA	55,0 (3)	56,0 (3)	57,0 (3)	59,0 (3)	61,0 (3)	62,0 (3)	63,0 (3)		
peration range	Evaporator	Cooling	Max.~Min.	°CDB				10~-45					
Refrigerant	Type / GWP							R-410A / 2.087,5	;				
	Charge			kg	5	,2		7,9		1	,5		
				TCO₂eq	10),9		16,5		24	1,0		
	Control						Elec	tronic expansion	valve				
ower supply	Phase/Freque	ncy/Voltage		Hz/V				3~/50/380-415					
	<u> </u>			DEO DVs									
vetom	Outdoor unit	nodulo 1	L	REQ-BY1		30	(1 D			40			
ystem						LREQ15BY				REQ20BY1R			
1-ful	Outdoor unit module 2					LREQ15BY			LI	REQ20BY1R			
errigerating capacity	tty Medium temperature Nom. kW Low temperature Nom. kW					67,8 (1)	<u> </u>		75,8 (1)				
						27,8				29,6			
ower input	Medium temperatu			kW		30,4				34,0			
	Low temperatu	e Nom.		kW		25,6		27,6					
ound pressure level	Nom.			dBA		65,0			66,0				
iping connections	Liquid							ø 19,05					
	Gas				ø 41,28								

(1) Cooling: evaporating temp. -10°C; outdoor temp. 32°C; suction SH10°C (2) Cooling: evaporating temp. -35°C; outdoor temp. 32°C; suction SH10°C (3) Sound pressure data: measured at 1m in front of unit, at 1.5m height | RLA is based on following conditions: outdoor temp. 32°CDB; suction SH 10°C; saturated temperature equivalent to suction pressure -10°C

LRMEQ, BY1




1	Gas pipe connection Ø19.1 brazing
2	Liquid pipe connection Ø9.5 brazing
3	(2X) Service port (in the unit)
4	Electronic connection and grounding terminal M5 (in the switch box)
5	Refrigerant piping intake
6	Power supply and output signal wiring intake (knockout hole Ø34)
7	Control wiring intake (knockout hole Ø27)
8	Drain outlet



3D111429

LREQ5,6BY1




No.	Parts name	Remarks
1	Liquid pipe connection port	ø 9.5
2	Gas pipe connection port	ø 22.2
3	Earth terminal	Inside of electric component box (M8)
4	Power cord routing hole (side)	ø 62
5	Power cord routing hole (front)	ø 45
6	Power cord routing hole (front)	ø 27
7	Power cord routing hole (bottom)	ø 50
8	Wire routing hole (front)	ø 27
9	Pipe routing hole (front)	
10	Pipe routing hole (bottom)	

NOTES

- Detail for front side and detail for bottom side indicate the dimensions after fixing the attached piping.
 ** is a size in the state where accessory piping is connected.

Detailed technical drawings

LREQ8-12BY1




No.	Parts name	Remarks
1	Liquid pipe connection port	ø 12.7
2	Gas pipe connection port	ø 28.6
3	Earth terminal	Inside of electric component box (M8)
4	Power cord routing hole (side)	ø 62
5	Power cord routing hole (front)	ø 45
6	Power cord routing hole (front)	ø 27
7	Power cord routing hole (bottom)	ø 65.5
8	Wire routing hole (front)	ø 27
9	Pipe routing hole (front)	
10	Pipe routing hole (bottom)	

NOTES

- 1. Detail for front side and detail for bottom side indicate the dimensions after fixing the attached piping.

 2. *** is a size in the state where accessory piping is connected.


LREQ15-20BY1



No.	Parts name Remarks	
1	Liquid pipe connection port	ø 12.7
2	Gas pipe connection port	ø 34.9
3	Earth terminal	Inside of electric component box (M8)
4	Power cord routing hole (side)	ø 62
5	Power cord routing hole (front)	ø 45
6	Power cord routing hole (front)	ø 27
7	Power cord routing hole (bottom)	ø 65.5
8	Wire routing hole (front)	ø 27
9	Pipe routing hole (front)	
10	Pipe routing hole (bottom)	

NOTES


- 1. Detail for front side and detail for bottom side indicate the dimensions after fixing the attached piping.
- 2. "*" is a size in the state where accessory piping is connected.



Daikin Condensing units with CO₂ refrigerant







CO₂ Condensing Units

Tewis

Standard Condensing units

Standard condensing units with transcritical cycle

- > Chassis in galvanized and painted steel sheet. Bodyworking and soundproofing available
- > High modular concept.
- > The gascooler can be disconnected from the unit
- > Electrical board with all the necessary electronics for the operation of the unit
- > 1 MT compressor
- > (Optional) Frequency drive
- > All piping done in stainless steel
- > Multiple options possible to facilitate transport of the unit
- > All necessary safety devices
- > 3 air exit configurations
- > Reduced dimensions
- > Easy to transport
- > Until 6 assembly options





F-Gas Free



Switchboard



Plug&Play



Electronic Control




Proportional Modulation




Heating Interchanger (Optional)




Protective Case














Clime

Global











Tewis a member of DAIKIN group

Small Booster Condensing units

Small condensing units with Transcritical cycle

- > Gas cooler with Axial or Radial EC fans.
- > Air connection:Three different configurations
- > V-shaped gas cooler optimized for CO2 applications
- Compressor configuration: CU:1x MT

Racks: $1 \times MT + 1 \times LT/2 \times MT$


- Racks Standard delivery:
 Inverter: 1x MT and 1x LT compressor
 CU: inverter optional
- High safety level with pressure relief valves, pressure switches and intelligent controls
- > Stainless steel Piping
- Galvanized and painted sheet metal chassis and weather proof enclosure.
- > Optional: acoustic insulation
- > Electrical Panel including electronic controller and control panel
- Modular concept The gascooler can be disassembled from the unit and assembled in different configurations




- > Reduced dimensions
- > Easy to transport
- > Until 6 assembly options



















CO, Condensing Units

Tewis


Large Booster Condensing units

Large condensing units with Transcritical cycle

- > Gas cooler with Axial or Radial EC fans.
- › Air connection: Three different configurations
- > (Optional) Heat recovery heat exchanger to take advantage of the "free heat" for air conditioning or for sanitary application
- Galvanized and painted sheet metal chassis and weather proof enclosure.
- > Optional: acoustic insolation
- > Large liquid receiver
- > All piping done in stainless steel
- > Design adapted for loading and transportation
- (Optional) Parallel compressor(s) to improve further the efficiency of the unit. Only for FCZ range where more than 2 compressor(s) can be used
- Compressor configuration Bitzer/Dorin: MT compressor(s)
 - Possibility to have combination of MT and LT compressor
- Racks Standard delivery: Inverter: 1x MT and 1x LT
- > Electrical Panel including electronic controller and control panel




- > High safety level with pressure relief valves, pressure switches and intelligent controls
- > Visible panel of manometers and pressostats
- > High modular concept.
- > The gascooler can be disconnected from the unit







FCZ3E












FCZ4E











FCZ4G













FCZ4F














Compressor packs & racks

Multi compressor units

- ☑ Open frame for multi-compressors racks
- ☑ Three or four compressors on parallel
- ☑ Many different compressor types
 - > Hermetic
 - > Hermetic Scroll (Brand: Copeland)
 - Semihermetic reciprocating (Brand: Bitzer, Dorin, Copeland Stream & Frascold)
 - Screw compressors: For LRV model is a single screw from J&E Hall and for LRS model Bitzer (twin screw)
 - Larger Refrigeration capacities or solution with screw compressors has to be selected from our technical department.
 - Consist in many models for medium and low temperature, with a refrigeration capacity up to 900,000 Watt.
- ☑ Compatible with latest refrigerants*



Standard features

- > Metal open frame with electrical switchboard
- Compressor parallel with discharge and suction header
- > Liquid receiver
- > Liquid line
- High and low pressure switch
- Electrical switchboard complete with electronic control

Most common used options:

- > Panels to close the frame and put it outside
- Oil equalization through mechanical floating valve
- > Oil equalization through electronic valve
- > Oversized liquid receiver
- > Refrigerant charge


Other options available on request

Single Screw compressor

The single screw compressor consists of a main single screw and two gate rotors. They are designed for high capacities and optimal performances through the step less capacity control.







LRE

Multi compressors rack unit with Scroll/Digital scroll and hermetic reciprocating compressors

General features:

- > Capacity for MT cooling: 7,2 kW to 26 kW
- > Capacity for LT cooling: 6,6 kW to 12 kW
- > Ambient temperature range : 25°C +43°C
- > R134A a, R 449A, R448A, R452A R407F depending on the used compressor
- Copeland scroll/digital scroll, Tecumseh and Maneurop reciprocation hermetic compressors
 Other types, brands and capacities are possible upon request
- > Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

Standard configuration:

Basic Frame Version:

Basic frame made from folded and pre-painted steel sheet, with complete closed frame with simple sound proof material and anti-vibration Supports (CC Standard)

Basic Refrigerating System:

The compressors (3 or 4) are connected in parallel, with one suction and discharge header. Each compressor is fitted with shut-off valves on suction line and discharge line.

The compressors are fixed to the frame through rubber anti-vibration supports.

The oil equalization system is composed of an oil separator and an equalization header, which are mounted on the compressor oil sight glass

According to the number of compressors fitted, there is one or two oil level indicator/s, fitted onto the equalization header.

The refrigerating system is equipped with liquid receivers, if there is more than one receiver, the installation is made in parallel with a safety valve, a dehydration cartridge filter, interchangeable, liquid level alarm, liquid sight glass and shut-off valves. On suction line there is a mechanical cartridge filter, interchangeable.



The refrigerating system is fitted with:

- General high pressure switch, adjustable and auto-resetting
- General low pressure switch, adjustable and auto-resetting
- > Emergency low pressure switch, adjustable and auto-resetting
- > Low pressure switches for each compressor emergency, adjustable and auto-resetting
- High pressure switches to control condenser fans, adjustable and auto-resetting
- Low pressure probe, placed on suction header for capacity control
- > High pressure gauge
- > Low pressure gauge
- > With or without integrated condenser

Electrical panel:

Standard power distribution

Disconnecting switch

Compressors protection, with overload cut-out motor protector; fuses for fans protection, thermo contacts for each single fan

Auxiliary circuit 230 volt through transformer 400V/230V

Electronic card XC440C

IP55 with greed and ventilation fan

On the door there is the electronic card and 4 lamps: emergency (button + lamp), fans block, high pressure switch block, low pressure

Switch block, and selector for on/off compressors. Condensation control through pressure switches: 1 pressure switch every 2 fans, standard 2 pressures

Accessories:

INSRD	Closed frame with double layer sound proofing material
AC&R	Mechanical oil equalization system with oil reserve, oil line filter, pressure reduction valve onto oil reserve
TRAXOIL	Electronic oil distribution system
INSRD	Closed frame with double layer sound proofing material

RIC. LIQ.	Oversized liquid receiver
CFF	Compressors sound shell
ELC.C	Electronic card EWCM4180 - XC1000D – EWCM9100
FQD	Frequency driver

Multi compressor rack unit with semi hermetic compressors

General features:

- > Capacity for MT cooling: 25 kW to 320 kW
- > Capacity for LT cooling: 13 kW to 133 kW
- > Ambient temperature range : 25°C +43°C
- > R134A, R 449A, R448A, R452A R407F
- > Reciprocating semi hermetic compressors:

LRB - Bitzer

LRD - Dorin

LRR - Frascold,

LRC - Copeland stream

Other types, brands and capacities are possible on request

> Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C



Basic Frame Version:

Basic frame made from folded and painted steel sheet, screwed with bolts to make a basic structure to fix the components on it.

Basic Refrigerating System:

The compressors (3 or 4) are connected in parallel, with only one suction and discharge header. Each compressor is fitted with shut-off valves on suction line and discharge line.

The compressors are fixed to the frame through rubber anti-vibration supports.

Compressors used for low temperature are complete with fan heads.

The oil equalization system is composed of an oil separator and an equalization header, which are mounted on the compressor oil sight glass connection.

According to the number of compressors fitted, there is one or two oil level indicator/s, fitted onto the equalization header.

The refrigerating system is equipped with liquid receivers, if there is more than one receiver, the installation is made in parallel with a safety valve, a dehydration cartridge filter, interchangeable, liquid level alarm, liquid sight glass and shut-off valves. On suction line there is a mechanical cartridge filter, interchangeable.



The refrigerating system is fitted with:

- > General high pressure switch, adjustable and auto-resetting
- > General low pressure switch, adjustable and auto-resetting
- > Oil pressure switch for each compressor
- > Emergency low pressure switch, adjustable and auto-resetting
- Low pressure switches for each compressor emergency, adjustable and auto-resetting
- > High pressure switches to control condenser fans, adjustable and auto-resetting (the pressure switches control 2 fans; if there are more than 4 condenser fans, the quantity of pressure switches installed increases to a maximum of 4)
- > Low pressure probe, placed on suction header for capacity control
- > High pressure gauge
- > Low pressure gauge

Electrical panel:

Standard power distribution

Disconnecting switch

Compressors protection, with overload cut-out motor protector, fuses for fans protection, thermos contacts for each single fan Auxiliary circuit 230 volt through transformer 400V/230V Electronic card XC440C

IP55 with greed and ventilation fan

On the door there is the electronic card and 4 lamps : emergency (button + lamp), fans block, high pressure switch block, low pressure

Switch block, and selector for on/off compressors Condensation control through pressure switches: 1 pressure switch every 2 fans, standard

Accessories:

INSRD	Closed frame with double layer sound proofing material	
AC&R	Mechanical oil equalization system with oil reserve, oil line filter, pressure reduction valve onto oil reserve	
TRAXOIL	Electronic oil distribution system	
INSRD	Closed frame with double layer sound proofing material	
CFF	Compressors sound shell	
FQD	Frequency driver	

RIC. LIQ.	Oversized liquid receiver
FREON	Refrigerant charge
ELC.C	Electronic card EWCM4180 - XC1000D – EWCM9100
CR1	CR1 Capacity controller
CR2	CR2 Capacity controller
CAP	Capacity step controled compressors



The final leap towards

natural refrigeration

Power and compressors

The compression sets are made up of 2 to 4 compressors except in the case of parallel compression, which adds up to 2 specific compressors.

BT

FULL SERIES 10 kW - 60 kW

MT



Transcritical booster




Traditional booster with parallel compression



Booster with condensation assistant

30 kW FULL BPC 240 kV

Subcritical booster with parallel compression





Efficiency improvement by modulation

One frequency inverter for each compression group adapts its function parameters to the system cooling necessities continuously saving energy and extending the service life of the machine.

Chassis

FullCO₂ models are available in sheet metal chassis, accesible 360° with option of housing and acoustic insulation.




Plug & play

The units are prepared for a very agile start-up at a mechanical and electronic level, with built-in electric panel.

Technology for Everyone

Automation and operation of the system are made with open technology standards. Thus the customer does not depend on a single manufacturer or installer, which decreases maintenance and repair costs.













temperature

compressors



Low temperature group

Covers freezing needs. Equipped with oil system, gas cooler connections and all necessary protection and safety elements.



Medium temperature group

It covers the refrigeration needs and allows the operation of the BT group. Equipped with oil system, gas cooler connections and all necessary protection and safety elements. Includes CO₂ receiver.



Auxiliary exchanger plates

They keep the plant at its optimum operating point when ambient temperatures are high.



Parallel compressor

The efficiency of the system is considerably increased.




Economizer

Increases the efficiency of the system by making the MT compressors give part of their power to the BT group.



Switchboard

Integrated and easy to use via touch screen, it displays an exclusive control software.



100% of pipes

Retrofit & external condensation

Our system offers the possibility to take advantage of an existing machine using it in ancillary functions and also, recover a large amount of gas, with the consequent savings.

FullBC & FullBPC models allow to assist the condensation of the CO_2 booster in different ways:

- > Using an already present unit (Retrofit).
- > Partially using equipment from another service such as air conditioning.
- > Installing a specific equipment recommended by Tewis.

Compressor packs & racks

Small Racks

Small transcritical units without condenser

- > Small dimensions: 1600 x 840 x 840 mm
- > Easy transportation
- > Complete switchboard with protections, according to European legislation
- > Switchboard includes an advanced control software to manage all the electrical and electronic switches of the machine
- > 2 compressors
- > Safety mode: In case of anomalous increase in temperature or pressure in the liquid zone, the safety equipment is activated by stabilizing the CO2 pressure.
- > Proportional modulation: A frequency inverter in each group of compressors adapts its operation to the specific demand of each moment, saving energy and prolonging the life of the plant. the current of a generator set and works even during a power cut.
- > Heat recovery (optional) which allows to take advantage of the heat generated by the system discharge for air conditioning or ACS.





F-Gas Free



Switchboard



Plug&Play



Electronic Control




Proportional Modulation




Heating Interchanger (Optional)



Protective Case







Conditions: LT: Tev.: -35°C SH: 8°K MT: Tev.: -10°C SH: 8°K Clime: Tev. med: 5°C SH: 8°K

> Mechanical MSC subcooler








Medium Racks


Transcritical units without condenser

- > Adapted design for loading and transportation
- > Integrated switchboard. Easy to use via touch screen and displays an exclusive control software
- Heat recovery (optional) which allows to take advantage of the heat generated by the system discharge for air conditioning or ACS.
- > Parallel compressor (optional).
- > The parallel compression includes one or two compressors that extract steam from the accumulation tank, lightening the load of the rest of the compressors and improving their efficiency index.
- > Possibility of incorporating up to 4 compressors
- > Proportional modulation: A frequency inverter in each group of compressors adapts its operation to the specific demand of each moment, saving energy and prolonging the life of the plant.
- > Mechanical subcooler exchanger, connected to an auxiliary unit that cools the discharge of the transcritical fluid, reducing steam and increasing the efficiency of the system

















Compressor packs & racks

Large Racks

Transcritical double units without condenser

- > Integrated switchboard. Easy to use via touch screen and displays an exclusive control software (see next page)
- > Parallel compressors (optional), which increase considerably the efficiency of the system
- > Possibility of incorporating up to 9 compressors
- > Low and Medium temperature compressors
- > Economizer: Increases the efficiency of the system by making the MT compressors give part of their power to the LT compressors group.
- > Proportional modulation: A frequency inverter in each group of compressors adapts its operation to the specific demand of each moment, saving energy and prolonging the life of the plant.
- > Mechanical subcooler exchanger, connected to an auxiliary unit that cools the discharge of the transcritical fluid, reducing steam and increasing the efficiency of the system
- > Stainless steel in 100% of the pipes





F-Gas Free

Plug&Play



Protective Case



Switchboard



Proportional Modulation



Electronic Control




Heating Interchanger (Optional)



Parallel compressors (Optional)



Mechanical Subcooler (Optional)



Conditions: LT: Tev.: -35°C SH: 8°K MT: Tev.: -10°C SH: 8°K

Clime: Tev. med: 5°C SH: 8°K



Mechanical subcooler







Switchboard & electronic control

Switchboard

- Bench-mounted switchboard, including complete wiring.
- \rightarrow Power supply at 400V / 3F + N / 50Hz
- Frequency inverter in the first compressor in sections BT, MT and parallel
- Booster components and remote gas coolers electrically protected against overcurrents and short circuits.
- > Option: electrical connections of power supply to the auxiliary unit




Electronic control

- It represents the best option for transcritical and subcritical CO₂ solutions with Booster circuit and allows to manage up to two circuits for the recovery of heat.
- Televis System compatible and open for the integration of Modbus RTU / TCP or BACnet MS / TP (optional) systems.
- > Touch screen with synoptic and real-time data.
- > Data logging and alarms.
- > Historical charts and data tables.
- > Parameter management.

























Service station (Ranst, Belgium) Conveni-Pack

Discover why a Belgian petrol station owner chose Daikin for its shop comfort and refrigeration needs. www.youtube.com/DaikinEurope







Conveni-Pack,


integrated solution for commercial refrigeration, heating and air conditioning

Why choose Conveni-Pack?

Competition in the retail food sector is fierce. This does not just affect the income you can earn from sales - operating costs are also a determing factor for success.


Energy efficient heat recovery system

- Conveni-Pack recovers up to 100% of the heat extracted from supermarket refrigeration cases and re-uses it to heat the retail space and improve shop comfort at no additional cost (heat recovery system)
- > Savings of up to 50% on energy costs
- Daikin inverter scroll compressor with economizer technology



Installing a compact solution

- > Easy to install, even in small spaces
- > Small footprint (up to 60% smaller footprint than conventional systems) and low weight
- > Reduced piping requirements
- > Minimal planning groundwork and lower assembly costs



Unique combination


 > First mass-produced, whole-building system to combine medium and low refrigeration, heating, air conditioning in one circuit


Reliable operation


- > Error-proof component selection
- > Factory leak-tested and pre-charged

Year-round climate comfort

- Quiet operation: Improved acoustics thanks to night operation mode, inverter control and inverter driven fans with optimised blades and grills
- High grade sound insulation on both panels and compressors
- > Specially designed fan blades to limit sound emissions
- > 4 low sound operation settings including night mode
- The heat recovered from refrigerated and freezer display cabinets can be used to provide heating for the shop.









Internationally awarded

Winner of several awards* thanks to the innovating technology used and environmental friendly solution offered:



- > Winner of UK Environmental Product of the Year, Cooling Industry Awards - 2006
- Winner of Incentive Prize, German Environment Ministry - 2007
- Winner of the Innovation Trophy, equipmag (exhibition in France) - 2008
- Winner of 2014 Institute of Refrigeration Ireland (IRI) Environmental award
- > Environmental Friendliness category of the Top Retail Product Awards 2014 in Germany

Reference

Edeka Buschkühle supermarket (Germany)

2 Conveni-Pack systems supply 32 meters of service counters, 12.5 meters of convenience fridges, one cooling storage room for fruit, an air curtain and 5 indoor units; the ZEAS system supplies two deep-freeze cabinets with a total capacity of 5 kW.



Discover more references on www.daikineurope.com/references

Benefits for installers/consultants

- Integrated electrical & control box
- Unit already pre-charged with refrigeran
- Established VRV technology ensuring optimised installation and maintenance
- > Reduced delivery time thanks to European manufacturing plant
- > Flexible system for multiple applications
- Connectable to all grocery refrigeration applications and supplied with a wide range of air conditioning indoor units to meet shop requirements
- Outdoor units can be positioned up to 35m above or 10m below the indoor units
- > Piping length possible up to 130m
- Suitable for indoor installation through the use of high ESP fans

Benefits for shop owners

- Thought design for supermarkets and smaller retail outlets
- Maximised retail sales space available as Conveni-Pack ha a footprint up to 60% smaller than conventional grocery refrigeration systems
- Reduced energy consumption by up to 50% through heat recovery
- Quiet operation, thus ideal for densely populated urban areas

Marketing tools

Refrigeration Xpress

User-friendly design software for Conveni-Pack, CCU, SCU and ZEAS condensing units. Its detailed report includes a list of materials, piping and wiring diagrams, and device options.



Short videos

 Watch a short animation on the unique refrigeration solution Conveni-Pack







LRYEQ-AY





Conveni-Pack refrigeration system with heat recovery

Refrigeration solution for food retailers featuring award winning technology for heat recovery

- Integrates high and low temperature refrigeration and air conditioning (including heating) into one system
- > By using heat recovery, optimised controls and state of the art compressor technology, Conveni-pack can reduce annual energy consumption up to 50% or more, compared to conventional systems
- Lower associated CO₂ emissions thanks to the heat pump technology
- > Conveni-pack's modular design allows it to be used for smaller as well as larger shops
- > The modularity of the Conveni-pack system maximises installation flexibility. Outdoor units can be grouped into blocks or rows, or distributed around the building, to meet individual installation constraints
- The heat extracted from the refrigeration showcases or evaporators can be re-used for comfort heating of the shop at no extra cost
- > Low sound level including "night mode" operation





Conveni pack, in combination with a ZEAS unit.

This store was nominated by spar as its 'local supermarket of the year', thanks in part to its owner's strategic investment in a key department: Refrigeration. By installing a Conveni pack in combination with Zeas, it was possible to **save around €10,000 on energy costs each year**, from money that would otherwise have spent on heating. **SPAR, Supermarket.**

Medium Temperatu	re Refrigeration			RYEQ-AY	16
Cooling capacity	Air conditioning	Nom.		kW	14,0 (1)
	Refrigeration	Nom.		kW	21,8 (2)
leating capacity	Air conditioning	Nom. kW		kW	27,0 (3)
	Refrigeration	Nom.		kW	21,8 (4)
Dimensions	Unit	Height		mm	1.680
		Width		mm	1.240
		Depth		mm	765
/eight	Unit			kg	370
eat exchanger	Туре				Cross fin coil
ompressor	Туре			İ	Hermetically sealed scroll compressor
	Piston displaceme	nt		m³/h	13,34
	Speed			rpm	6.300
	Output			w	2.500
	Starting method				Direct on line (inverter driven)
	Frequency ON/OF	F			Less than 6 times/hour
Compressor 2	Speed			rpm	2.900
	Output			W	3.600
ompressor 3	Speed			rpm	2.900
	Output			W	4.500
an	Туре				Propeller fan
	Quantity				2
	Air flow rate	Cooling	Nom.	m³/min	230
an motor	Output			W	750
	Drive				Direct drive
ound pressure level	Nom.			dBA	62,0
peration range	Evaporator	Cooling	Min.~Max.	°CDB	-20~10
	Cooling	Ambient	Min.~Max.	°CDB	-5~43
	Heating	Ambient	Min.~Max.	°CDB	-15~21
efrigerant	Type				R-410A
	GWP				2.087,5
	Charge			kg	11,5
				TCO₂eq	24,0
	Control				Electronic expansion valve
ower supply	Phase/Frequency/	Voltage		Hz/V	3~/50/380-415

(1) Cooling priority mode: indoor temp. 27°CDB, 19°CWB; outdoor temp. 32°CDB; piping length: 7.5m; level difference: 0m (2) Cooling priority mode: evaporating temp. -10°C; outdoor temp. 32°CDB; Suction SH: 10°C (3) Heat recovery 100% mode: indoor temp. 20°CDB; outdoor temp. 7°CDB, 6°CWB; refrigeration load 18kW; piping length: 7.5m; level difference: 0m (4) Saturated temperature equivalent to suction pressure (refrigeration side): -10°C (under chilled condition); connection capacity for indoor air conditioner: 10HP, when heat recovery is 100%

Indoor units and Biddle air curtains for connection to Conveni-Pack

To respond to all shop requirements for comfort cooling and heating, a wide range of air conditioning indoor units and Biddle air curtains are available.

Capacity class (kW)

Model	Product name	50	63	71	80	100	125	140	200	250
Cooling capacity (kW) ¹		5,6	7,1	8,0	9,0	11,2	14,0	16,0	22,4	28,0
Heating capacity (kW) ²		6,3	8,0	9,0	10,0	12,5	16,0	18,0	25,0	31,5
Round flow cassette	FXFQ-A	•	•		•	•	•			
2-way blow ceiling mounted cassette	FXCQ-A	•	•		•		•			
Ceiling mounted corner cassette	FXKQ-MA		•							
Concealed ceiling unit with inverter driven fan	FXSQ-A	•	•		•	•	•			
Concealed ceiling unit with inverter driven fan	FXMQ-P7	•	•		•	•	•			
Large concealed ceiling unit	FXMQ-MB								•	•
Ceiling suspended unit	FXHQ-A		•			•				
4-way blow ceiling suspended unit	FXUQ-A			•		•				
Floor standing unit	FXLQ-P	•	•							
Concealed floor standing unit	FXNQ-A	•	•							


Capacity class (kW)

Model	Product Name	1	80	100	125	140	200	250
Heating capacity (kW) ²			7,4 - 9,2	11,6 - 13,4	15,6	16,2 - 19,9	29,4	29,4 - 31,1
Biddle air curtain free hanging	CYVS-DK		•	•	•	•	•	•
Biddle air curtain cassette	CYVM-DK		•	•	•	•	•	•
Biddle air curtain recessed	CYVL-DK	COLUMN TO SERVICE SERV	•	•	•	•	•	•


Nominal cooling capacities are based on: indoor temperature: 27°CDB / 19°CWB, outdoor temperature: 35°CDB, piping length: 7,5m, level difference: 0m

² Nominal heating capacities are based on: indoor temperature: 20°CDB, outdoor temperature: 7°CDB / 6°CWB, piping length: 7,5m, level difference: 0m

LRYEQ16AY



LRYEQ-AY




LCBKQ-AV1



Booster unit


- > A booster unit allows to connect freezer showcases / rooms to ZEAS and Conveni-Pack outdoor units
- > Reduced piping requirements, from 4 to 2 pipes, compared to a conventional system
- > Low sound mode available reducing sound emissions significantly without giving in on Refrigerating capacity





Booster with Conveni-Pack:

MEDIUM + LOW TEMPERATURE refrigeration + space air conditioning + Biddle air curtain



Low Temperature Re	efrigeration		LC	CBKQ-AV1	3
Refrigerating capacity	Low temperature		Nom.	kW	3,35 (1)
Dimensions	Unit	Height		mm	480
		Width		mm	680
		Depth		mm	310
Weight	Unit	kg			47
Compressor	Туре				Hermetically sealed swing compressor
	Piston displacemen	nt		m³/h	10,16
	Number of revolut	ions		rpm	6.540
	Output			W	1.300
	Starting method				Direct on line (inverter driven)
	Frequency ON/OFF	:			Less than 6 times/hour
Fan	Type				Propeller fan
	Air flow rate	Cooling	Nom.	m³/min	1,6
Operation range	Evaporator	Cooling	Min.~Max.	°CDB	-45~-20
	Ambient temperature	Min.~Max.		°C	-15~43
Refrigerant	Туре				R-410A
	GWP				2.087,5
	Control				Electronic expansion valve
Piping connections	For outdoor unit	Liquid	OD	mm	6,35
	To indoor unit	Liquid	OD	mm	6,35
	For indoor unit	Gas	OD	mm	15,9
	To outdoor unit	Gas	OD	mm	9,5
Power supply	Phase/Frequency/	Voltage		Hz/V	1~/50/220-240



Medium temperature with air conditioning

1+2 (max. 3)

2+2 (max. 4)

2+3 (max. 5)



Mini racks

✓ MT + Air conditioning (with or w/o condenser)

FNB 18 kW FNV58 27 kW 1.560 mm 45 kW



Racks

✓ MT + Air conditioning
(with or w/o condenser)

FCCE 2.120 mm 18 kW 52 kW

✓ MT + Air conditioning (with or w/o condenser)

FCZ4F 2.660 mm 85 kW

FCZ4G 36 kW FCCG 93 kW 3.060 mm 108 kW

Duplex racks

✓ MT + Air conditioning (with or w/o condenser) 5+4 (max. 9)

FUJ 4.000 mm 230 kW



Conditions: LT: Tev.: -35°C SH: 8°K

MT: Tev.: -10°C SH: 8°K

Clime: Tev. med: 5°C SH: 8°K




Low temperature with air conditioning








Racks





Duplex racks



108 kW

Clime




Global









Evaporators range

Evaporators with or without TEV for different operations and refrigerants

General features:

- > Capacity for LT/MT cooling: 0,5 to 213 kW
- > Ambient/cooling room temperature range: 40°C +25°C
- > Refrigerants: R134A a, R 449A, R448A, R452A R407F, R 407A
- > Fin distance: from 3 mm to 11 mm
- > Fin materials: Al
- > Tube materials: Cu
- > Conditions:

MT: Ambient temperature: 35°C Evp. Temperature: -10°C LT: Ambient temperature: 35°C Evp. Temperature: -35°C

Options:

- > Electric defrost heating
- > Hot gas defrost
- > Drain pan heating
- > Fan ring heater
- › High efficient EC fans
- > Wiring on terminal box
- > Included valves and regulation
- > Fin materials AISI 304, AISI 316
- > Tube materials AISI 304, AISI 316
- > Casing in stainless steel (Inox)




Types:


- > flat evaporator
- > double flow
- > cubic design
- > Evaporator only
- > Evaporator + EEV/TEV
- > Evaporator + EEV/TEV + electronic controller

Dimensions


Flat




mm	A	В	С
201	215	614	410
202	215	1034	410
203	215	1614	410
232	150	713	455
301	300	910	690
302	300	1530	690
303	300	2150	690
304	300	2770	690
305	300	3390	690












mm	Α	В	С	D	E
231	171	579	585	293	600
232	171	889	585	603	600
233	171	1199	585	913	600
234	171	1509	585	1223	600
352	300	1671	995	1214	1065
353	300	2291	995	1834	1065
354	300	2911	995	2454	1065
355	300	3531	995	3074	1065




Cubic





mm	Α	В	C	D	E
301	420	480	789	495	345
302	420	480	1254	960	345
303	420	480	1719	1425	345
HEU351	545	690	805	605	540
HEU352	530	690	1220	965	540
HEU353	600	690	1690	1370	540
HEU403	620	700	1840	1520	545
HEU502	844	992	1829	1526	740
SKC352	490	606	1614	1270	450
SKC353	490	606	2234	1890	450
SKC452	610	650	2032	1680	510
SKC503	800	830	3350	2760	675



Other products

Model Refrigerant Capacity range

Large- Monoblock for wall mounting

LMH Industrial type Standard refrigerant: MT: R134a, LT: R452A Other refrigerants possible upon request



0° 2,5 to 28,9kW

-20°) 2,5 to 28,6kW

Large- Monoblock for shock freezing

LMH

Direct mounting trough the wall Standard refrigerant: MT: R134a, LT: R452A Other refrigerants possible upon request



-40°) 11,8 to 13,5 kW

Open frame condensing units with Bitzer semi hermetic compressor

LA

Standard refrigerants:
R134a, R407H, R449A
Other refrigerants upon request
Semi hermetic Bitzer compressor
Liquid receiver with safety
pressure relief valve for PED units
Many different options and
accessories available upon request.



-10°) 3,26 to 29,5 kW

-30°) 1,1 to 24 kW

 $\label{eq:bibliosis} \begin{tabular}{ll} Mid to Large Bi-Block with cubic evaporator \\ LBH/LBK \end{tabular}$

MT: R134a, LT: R452A, R407F Other refrigerants possible upon request





0°) 14,3 to 25,28 kW

Other products

Model Refrigerant **Capacity range** MT: R134a, LT: R452A, R407F Mid to Large Bi-Block with cubic Other refrigerants possible evaporator upon request 10,9 to 66,1 kW LBJ/LBM 4,6 to 32,45 kW MT: R134a, LT: R452A, R407F Commercial Biblock model for Other refrigerants possible -10°) 4,7 to 15 kW workrooms upon request LBHD / LBEH 19,4 to 197 kW 16,3 to 165,2 kW Standard Refrigerant: Water Chiller MT: R134a, R449A LWW (water cooled) 13,3 to 86 kW LWA (air cooled) -20° 10,6 to 69,1 kW



Hubbard

Products

Hubbard Products has an enviable global reputation for innovation and excellence in refrigeration design, refrigeration engineering and refrigeration solutions for static and transport refrigeration requirements.

Hubbard serves the cool chain supply sector offering a wide range of direct drive, alternator drive, Diesel drive and stand alone electrical units for panel vans, box body vehicles and truck and trailer combinations.

- > Cellar Cooling
- > Convenience and Retail Cooling
- > Multi Compressor Packs
- > Cold Room Units
- > Heat Recovery Systems
- > Transport Refrigeration
- > Low GWP, natural refrigeration systems

Hubbard Products Ltd., is one of the UK's leading designers, manufacturers and suppliers of energy-efficient commercial cooling equipment and has earned a Global reputation for innovation and design-led excellence.











Made to

Order



Made to Order

We build units according to customer requirements.


Our refrigeration experts are able to give the best advice, personalised to each situation.

We can provide complete solutions, entirely tailored to the customer needs.

Contact us to find the best solution for your business.



Please contact the refrigeration department at Daikin Europe (refrigeration@bxl.daikineurope.com) or your local refrigeration product manager.



Options

for ZEAS and Conveni-Pack

		Conveni-Pack				ZEAS				Multi	-ZEAS
_		LRYEQ16AY	LREQ5BY1	LREQ6BY1	LREQ8BY1	LREQ10BY1	LREQ12BY1	LREQ15BY1	LREQ20BY1	LREQ15BY1Rx2	LREQ20BY1Rx
Digital pressure ga	uge kit		,			BHGP26	5A1		,		
Pressure gauge kit		-	KHGP26B140								
	(a+b+c+d) kit	KPS26C504	KPS2	6C160		KPS26C280			KPS2	6C504	
	a. Air outlet	KPS26C504T	KPS26	C160T		KPS26C280T			KPS26	C504T	
Snowbreak hood*	b. Air inlet (left)	KPS26C504L	KPS26C504L KPS26C504L								
	c. Air inlet (right)	KPS26C504R	KPS26C504R KPS26C504R								
	d. Air inlet (rear)	KPS26C504B	KPS26	C160B		KPS26C280B			KPS26	C504B	
Central drain pan k	it	KWC26C450**	KWC2	6C160	KPS26C280		KPS26C450		KPS26C450*** x2		
Modbus communi	cation kit		BRR9A1V1							BRR9A1V1****	
Booster unit		ECDINGS/AV19							-		
Suction branch pip	e for multi	-				-				EKHRQ:	ZM****
		KHRQM22M29H8									
Refnet header		KHRQ22M64H8									
			KHRQM22M75H8								
						KHRQ22M2	20TA8				
Refnet joint		KHRQ22M29T9									
nemerjonie		KHRQ22M64T8									
						KHRQ22N	75T8				
ntelligent Conti	roller	DSC601C51					-				
Intelligent Man	ager	DCM601A51					-				

^{*} Snowbreak hoods are field-supplied. For technical drawings and more information, contact your dealer. It is recommended to install a snowbreak hood when regular snowfall occurs.

** In cold areas, provide a drain pan heater (field supply) to prevent drained water from freezing up in the drain pan

**** required for each module

***** software update required (to be executed during commissioning)


***** mandatory

Digital pressure gauge kit

BHGP26A1

The digital measurement display allows you to diagnose a unit at a glance and it can be used with all ZEAS units and Conveni-Pack systems.

- > Digital measurement display for fixed installation or service applications.
- > Displays high and low pressure.
- > Displays error codes in the event of a fault.
- > Displays up to 32 operating parameters.
- > Displays error code history (last three).
- > Scrolls and stores output values.
- Automatically returns to normal operating display mode.





Modbus communication kit

BRR9A1V1

The Daikin Modbus Communication Interface lets you fully integrate Daikin ZEAS and Daikin Conveni-Pack systems with building control automation networks and other monitoring systems.

The interface allows you to read all the operational parameters and control important values using the Modbus protocol. This unifying component transforms ZEAS and Conveni-Pack into a transparent, customisable refrigeration unit and means that you can create object-specific and energy-optimised shop concepts, including remote monitoring application.

Pro interfaces can be used to connect up to 32 ZEAS units, and are also suitable for use with Conveni-Pack systems and the Booster.

Control values

- > Target evaporation temperature
- > Low pressure level for on and off points
- > Forced stop
- > Error messages can be cancelled remotely



Display values

- > Model information and operating status
- > Refrigerant operating pressure and temperatures
- Electrical operating data and temperatures for components
- > Target values
- > Fan stage and compressor frequency, operating hours
- Warning and error messages as well as system safety functions

Options

Monoblock, Biblock and Wineblock

0.00		Medium tempera	ture applications	Low temperature applications		
Options Monoblock units	Option code	LMSMD	LMCMD	LMSLN	LMCLN	
Electronic control panel (MIR 90)	D.CNT CTR	•	No	Yes	No	
Cable for door switch connection	D.MIC.POR	Yes (only in combination with D.CNTR.CTR option)	No	Yes (only in combination with D.CNTR.CTR option)	No	
Remote control panel (5 m cable length)	D.PAN.SNG	Yes (only in combination with D.CNTR.CTR option)	No	Yes (only in combination with D.CNTR.CTR option)	No	
Common remote control panel for multiple units	D.PAN.MUL	Yes (only in combination with D.CNTR.CTR option)	Yes	Yes (only in combination with D.CNTR.CTR option)	•	
Longer remote control panel cable (till 10 m)	D.CAV PRM 10 mt	Yes (only in combination with D.CNTR.CTR option)	Yes	Yes (only in combination with D.CNTR.CTR option)	•	
Longer remote control panel cable (till 15 m)	D.CAV PRM 15 mt	Yes (only in combination with D.CNTR.CTR option)	Yes	Yes (only in combination with D.CNTR.CTR option)	•	
winter kit 1 full: Condenser fan pressure switch + Compressor crankcase heater + Supplemental solenoid valve on the discharge line	D.PRS VNT + D.RES CAR + D.SOL.SBR	•	(cap ≥ 300: included)	•	• (cap ≥ 300: included)	
Winter kit 2 basic: Condenser fan speed regulator (temperature controlled)	D.VVE.TER	No	only for 300	No	No	
Winter kit 2 full: Condenser fan speed regulator (temperature controlled) + Compressor crankcase heater + Supplemental solenoid valve on the discharge line	D.VVE.TER + D.RES CAR + D.SOL.SBR	(cap ≥ 200: included)	(cap ≥ 300: included)	(cap ≥ 300: included)	(cap ≥ 300: included)	
Winter kit 3 basic: Condenser fan speed regulator (Pressure controlled)	D.VVE.PRS	No	only for 300	No	No	
Winter kit 3 full: Condenser fan speed regulator (pressure controlled) + Compressor crankcase heater + Supplemental solenoid valve on the discharge line	D.VVE.PRS + D.RES CAR + D.SOL.SBR	(cap ≥ 200: included)	(cap ≥ 300: included)	(cap ≥ 300: included)	(cap ≥ 300: included)	
Anti-corrosion treatment (cataphoresis) on condenser coil	D.FRS CND	•	•	•	•	
Anti-corrosion treatment (cataphoresis) on evaporator coil	D.FRS EVP	•	•	•	•	
Voltage monitor	D.MON TEN	•	•	•	•	
Nater-cooled condenser (water from net) with oressure controlled water valve	D.CON ACQ	•	•	•	•	
switchboard heater	D.QUA.RIS	•	Only for cap ≥ 060	•	Only for cap ≥ 060	
Centrifugal fan kit	D.VNT.CEN	•	Only for cap ≥ 060	•	Only for cap ≥ 060	
Serial output	D.KIT.SUP	•	•	•	•	

Oution - Bible de contr		Medium tempera	ture applications	Low temperature applications		
Options Biblock units	Option code	SB.LBTMD	SB.LBCMD	SB.LBTLN	SB.LBCLN	
Common remote control panel for multiple units	D.PAN.MUL	No	•	No	•	
Longer remote control panel cable (till 10 m)	D.CAV PRM 10 mt	•	•	•	•	
Longer remote control panel cable (till 15 m)	D.CAV PRM 15 mt	•	•	•	•	
Fixed calibration high pressure switch AR	D.PRS HPF	Only Cap ≥ 100	Only Cap ≥ 100	Only Cap ≥ 172	Only Cap ≥ 172	
Winter kit 2 basic: Condenser fan speed regulator (temperature controlled)	D.VVE.TER	•	•	•	•	
Anti-corrosion treatment (cataphoresis) on condenser coil	D.FRS CND	•	•	•	•	
Anti-corrosion treatment (cataphoresis) on evaporator coil	D.FRS EVP	•	•	•	•	
Voltage monitor	D.MON TEN	•	•	•	•	
Water-cooled condenser (water from net) with pressure controlled water valve	D.CON ACQ	•	•	•	•	
switchboard heater	D.QUA.RIS	•	•	•	•	
Serial output	D.KIT.SUP	•	•	•	•	
Liquid line solenoid valve	D.SOL.LIQ	No	•	No	•	

Options Wineblock units (mono- as well as biblock models)	Options	LMSWHD	SB.LBCWHD SB.LBWWHD
Anti-corrosion treatment (cataphoresis) on condenser coil	D.FRS CND	•	•
Anti-corrosion treatment (cataphoresis) on evaporator coil	D.FRS EVP	•	•
Voltage monitor	D.MON TEN	•	•
Water-cooled condenser (water from net) with pressure controlled water valve	D.CON ACQ	•	•
Serial output	D.KIT SUP	•	•
Winter kit 2 basic: Condenser fan speed regulator (temperature controlled)	D.VVE.TER	•	•
Winter kit 3 basic: Condenser fan speed regulator (pressure controlled)	D.VVE.PRS	•	•

Condensing units

		Condensing unit fo	Twin condensing unit for outdoor installation	
		with hermetic compressors	with semi hermetic compressors	with twin-semi hermetic
RES CAR	Crankcase heater	•	•	•
PRO TRM	Thermal overload protection	•	•	•
VVE BCO	BESTCOP Condenser fan speed controller	•	•	•
VVE PRS	Pressure condenser fan speed controller	•	•	•
VVE TER	Temperature condenser fan speed controller	•	•	•
PRS LPF	LP switch (fixed calibration)	•	•	•
SEP ASP	Suction liquid separator	•	•	•
SEP OIL	Oil separator	•	•	•
VEN RAD	Radial type condenser fans	•	•	•
REG POT	Compressors capacity controller	•	•	•
SOL LIQ	Liquid line solenoid valve	•	•	•
CON ACQ	Watercooled condensation	•	•	•
VLT DIF	Different voltage	•		
FRS CND	Anti-corrosion protection on condenser coil	•	•	•
FRS EVP	Anti-corrosion protection on evaporator coil	•	•	•
IMB FUM	Fumigation according to ISPM15	•	•	•
PRS VNT	Condenser fan pressure switch	•	•	•
PRS HPR	HP switch with auto reset	•	•	•
MON TEN	Voltage monitor	•	•	•
INS SEM	Simple low noise housing	•	•	•
INS DOP	Enhanced low noise housing	•	•	•
QUA ELE	Power control box with magneto thermic switches	•	•	•
RES CAR	Crankcase heater	•	•	•
FQD	Frequency driver		•	•

		Multi compressor condensing unit	
		with scroll/digital scroll compressors	with semi hermectic compressors
INSRD	Closed frame with double layer sound proofing material	•	•
AC&R	Mechanical oil equalization system with oil reserve, oil line filter, pressure reduction valve onto oil reserve	•	•
TRAXOIL	Electronic oil distribution system	•	•
RIC.LIQ.	Oversized liquid receiver	•	•
CFF	Compressors sound shell	•	•
ELC.C	Electronic card EWCM4180 - XC1000D - EWCM9100	•	•

















Notes

Notes



Daikin refrigeration products are designed to reduce environmental impact. That's why Daikin ZEAS and Conveni-Pack already comply with the latest F-gas regulation. This secures your investments and enables you to plan ahead for long-term projects, already complying with all the regulations.



 $\textbf{Daikin Europe N.V.} \quad \text{Naamloze Vennootschap Zandvoordestraat 300} \cdot 8400 \ \text{Oostende} \cdot \text{Belgium} \cdot \text{www.daikin.eu} \cdot \text{BE 0412 120 336} \cdot \text{RPR Oostende (Publisher)}$



CPEN18-800



The present publication is drawn up by way of information only and does not constitute an offer binding upon Daikin Europe N.V. Daikin Europe N.V. has compiled the content of this publication to the best of its knowledge. No express or implied warranty is given for the completeness, accuracy, reliability or fitness for particular purpose of its content and the products and services presented therein. Specifications are subject to change without prior notice. Daikin Europe N.V. explicitly rejects any liability for any direct or indirect damage, in the broadest sense, arising from or related to the use and/or interpretation of this publication. All content is copyrighted by Daikin Europe N.V.

Printed on non-chlorinated paper.